




DIN 963 A

~ISO 2009

4.8

Norme abrogée



BN 20244

Vis à tête fraisée

à fente

Acier 4.8

zingué avec passivation épaisse

- ~UNI 6109
- ~ČSN 021151



Toutes les longueurs avec filetage ~ sous tête
Dimensionner les fraisures selon les normes correspondantes!

Article#	d ₁	d ₂ max.	k max.	n	t min.	L
3371032	M2	3,8	1,2	0,5	0,4	4
3371033						5
3371034						8
3371030						10
3371031						12
3371039	M2,5	4,7	1,5	0,6	0,5	4
3371040						5
3371041						6
3371042						8
3371035						10
3371036						16
3371037						20
3371051	M3	5,6	1,65	0,8	0,6	4
3371053						5
3371054						6
3371055						8
3371043						10
3371044						12
3371045						16
3371046						(18)
3371047						20
3371048						25
3371049						30
3371050						35
3371052						40
3371064	M4	7,5	2,2	1	0,8	5

Article#	d ₁	d ₂ max.	k max.	n	t min.	L
3371066	M4	7,5	2,2	1	0,8	6
3371068						8
3371056						10
3371057						12
3371058						(14)
3371059						16
3371060						20
3371061						25
3371062						30
3371063						40
3371065						50
3371067						60
3371077	M5	9,2	2,5	1,2	1	6
3371079						8
3371069						10
3371070						12
3371071						16
3371072						20
3371073						25
3371074						30
3371075						35
3371076						40
3371078						60
3371089	M6	11	3	1,6	1,2	8
3371080						10
3371081						12
3371082						16
3371083						20
3371084						25
3371085						30
3371086						35
3371087						40
3371088						50
3371090	M8	14,5	4	2	1,6	12
3371091						16
3371092						20
3371093						25
3371094						30
3371095						35
3371096						50
3371097						60

Article#	d ₁	d ₂ max.	k max.	n	t min.	L
3371026	M10	18	5	2,5	2	20
3371027						30
3371028						40
3371029						60