

7仕様

7-1. 共通仕様

型式	EH□-M1		EH□-M2		EH□-M3	
定格電圧	DC12 V～DC24 V		AC100 V～AC240 V (50/60 Hz)		DC12 V～DC48 V	
電圧許容範囲	DC10.8 V～DC35 V		AC90 V～AC264 V (50/60 Hz)		DC10 V～DC60 V	
使用周囲温度	-20℃～+50℃					
使用周囲湿度	85% RH以下、結露なきこと					
保存周囲温度	-30℃～+60℃					
保存周囲湿度	85% RH以下、結露なきこと					
取付場所	屋内 / 屋外					
取付方向	正・横・逆方向					
保護等級	IP65 (IEC 60529)					
条件	正方向取付					
絶縁抵抗	電源充電部と非充電金属部間DC500 Vメガにて1 MΩ以上					
耐電圧	電源充電部と非充電金属部間		電源充電部と非充電金属部間		電源充電部と非充電金属部間	
	AC500 Vにて1分間		AC1500 Vにて1分間		AC1000 Vにて1分間	
耐振動	45.0 m/s ² JIS C 60068-2-6:2010 (正方向取付)					
	70.0 m/s ² JIS D 1601-1995 3種B種 (EH□-M3のみ、推奨品の防振ゴムを使用、正方向取付) 推奨品：くら形防振ゴム 倉敷化工製 KE-30(RoHS対応品)					
耐衝撃	250 m/s ² 6 ms 1000回 (3軸1方向)、500 m/s ² 11 ms 3回 (3軸両方向) JIS C 60068-2-27:2011(正方向取付)					
質量(公差：±10%)	1.25 kg					
音量調整	ボリューム調整：Min～Max.					
	減音入力：通常音量から指定音量減音 (設定による)					
対応メモリーカード	SDカード / SDHCカード					
	推奨SDカード：SDV-2GP (オプション品)					
SDカードフォーマット	FAT16、32					

7-2. MP3仕様 (EHVのみ)

再生ファイル	MPEG1-Audio Layer III (MP3 サンプリング周波数44.1kHz)
対応ビットレート	32 kbit/s、64 kbit/s (標準)、128 kbit/s
	固定ビットレート(CBR)のみ
最大再生時間	合計220秒 (標準ビットレート再生、1ファイルの連続したMP3の場合)
内部メモリーサイズ	2 MByte (管理領域を含む)
備考	MPEG Layer-3 audio coding technology licensed from Fraunhofer IIS and Thomson Licensing.
	Joint Stereo and Dual Channelは使用できません。

7-3. 個別仕様


型式		EHV		EHS	
音圧レベル	アラーム	最大：110 dB (開口部より正面方向/at 1 m アラーム「ブルル」再生時)			
	MP3	最大：105 dB (開口部より正面方向/at 1 m MP3データ -6 dB 1 kHz正弦波再生時)			
定格消費電力	標準	EH□-M1	4.0 W (無電圧・NPN、DC12 V時)		5.0 W (無電圧・NPN、DC12 V時)
			5.0 W (有電圧・PNP、DC24 V時)		5.9 W (有電圧・PNP、DC24 V時)
		EH□-M2	5.3 W (AC240 V時)		6.9 W (AC240 V時)
		EH□-M3	5.6 W (DC48 V時)		5.1 W (DC48 V時)
	条件	ボリューム最大、MP3データ -6 dB 1 kHz正弦波再生		ボリューム最大、アラーム「ピーポーポー」再生	
再生音		MP3データ / アラーム・メロディ (固定)		アラーム・メロディ (固定)	
再生チャンネル数		ビット入力：8 / バイナリ入力：63		ビット入力：8 / バイナリ入力：32	
再生起動時間		300 ms以下 (信号起動・電源起動)			

7-4. 適合規格

適合規格	EH□-M1	EH□-M2	EH□-M3
EMC指令 (EN 61000-6-4, EN 61000-6-2)	○	-	-
EMC指令 (EN 13309)	-	-	○
RoHS指令 (EN IEC 63000)	○	- ※1	- ※1
UL 464, CSA-C22.2 No. 205-M1983	○ ※2	○ ※2	-
FCC Part15 SubpartB Class A	○	○	-
KC (KN32, KN35)	○	○	-

(備考)
・RoHS指令の閾値を超える規制物質の含有はありません。(※1)
・UL Listed (File No.S24210) (※2)
・EMCレベルは、ECE Regulation No.10 のレベルを満足する。(EH□-M3のみ)

7-5. 外形寸法(mm)



7Specifications

7-1 Standard Specifications

Model		EH□-M1		EH□-M2		EH□-M3	
Rated Voltage		12-24 V DC		100-240 V AC 50/60Hz		12-48 V DC	
Operating Voltage Range		10.8-3.5 V DC		90-264 V AC 50/60Hz		10-60 V DC	
Operating Ambient		-20 °C to 50 °C					
Operating Ambient Humidity		85 % or less RH (no condensation)					
Storage Ambient		-30 °C to 60 °C					
Storage Ambient Humidity		85 % or less RH (no condensation)					
Mounting	Location	Indoor / Outdoor					
	Position	Upright, Sideways, Inverted (Case is to be pointed in downward direction)					
Protection Rating		IP65 (IEC 60529)					
Condition		Upright Position					
Insulation Resistance		More than 1MΩ at 500V DC between terminal and chassis					
Withstand Voltage		Voltage applied between terminal and chassis without breaking insulation.					
		500 V AC for 1 min.		1500 V AC for 1 min.		1000 V AC for 1 min.	
Vibration Resistance		45.0 m/s ² IEC 60068-2-6:2007					
		70.0 m/s ² JIS D 1601-1995 Class 3 Class B					
		(It is recommended only for the EH□-M3 to attach in the upright position when using the Vibration Absorption Rubber) Recommended Parts: Vibration Absorption Rubber KE-30 (Kurashiki Kako Co., Ltd.) (RoHS Compliant)					
Impact Resistance		250m/s ² 6ms 1000times (one direction each of 3 axis), 500m/s ² 11ms 3times (both directions each of 3 axis) IEC 60068-2-27:2008					
Mass (Tolerance ±10%)		1.25 kg					
Volume Adjustment		Volume adjustable from minimum to maximum					
		Sound reduction input to reduce from current level (depending on settings)					
Supported Memory Card		SD Card, SDHC Card					
		Recommended SD Card: SDV-2GP (Option)					
File Format		FAT16, 32					

7-2 MP3 Specifications (EHV)

Playback File	MPEG1-Audio Layer III (MP3, Fs:44.1kHz)
Available Bit Rates	32 kb/sec., 64 kb/sec. (Standard), 128 kb/sec.
	Constant bit rate (CBR) Only
Maximum Playback Time	Total of 220 sec. (at standard bit rate, one MP3 file)
On-board Memory Size	2 MByte (including management domain)
Remarks	MPEG Layer-3 audio coding technology licensed from Fraunhofer IIS and Thomson Licensing.
	Joint Stereo and Dual Channel not available.

7-3 Model Specially Specifications

Model		EHV		EHS		
Sound Pressure Level	Alarm		Max : 110 dB (Directly in front at 1m from horn, alarm Stutter (rapid intermittent))			
	MP3		Max : 105 dB (Directly in front at 1m and -6 dB 1 kHz sound playback)			
Rated Power Consumption	Standard	EH□-M1	4.0 W (Non-voltage contact ・ NPN, at 12 V DC)		5.0 W (Non-voltage contact ・ NPN, at 12 V DC)	
			5.0 W (Voltage contact ・ PNP, at 24 V DC)		5.9 W (Voltage contact ・ PNP, at 24 V DC)	
		EH□-M2	5.3 W (at 240 V AC)		6.9 W (at 240 V AC)	
		EH□-M3	5.6 W (at 48 V DC)		5.1 W (at 48 V DC)	
	Condition		Maximum Volume with -6 dB 1 kHz sound)		Maximum Volume with "Rapid Hi-Lo" sound playback	
	Playback Sound		MP3 Data / Alarm / Melody (Standard)		Alarm / Melody (Standard)	
Playback Channel Inputs		Bit : 8 / Binary : 63		Bit : 8 / Binary : 32		
Playback Delay Time		300 ms or less (At Signal / Power Input)				


7-4 Conformity Standards

Conformity Standards	EH□-M1	EH□-M2	EH□-M3
EMC Directive (EN 61000-6-4, EN 61000-6-2)	○	-	-
EMC Directive (EN 13309)	-	-	○
RoHS Directive (EN IEC 63000)	○	- ※1	- ※1
UL 464, CSA22.2 No. 205-M1983	○ ※2	○ ※2	-
FCC Part15 SubpartB Class A	○	○	-
KC (KN32, KN35)	○	○	-

(Remarks)
・There are no contents of controlled substances exceeding the threshold for the RoHS Directive. (※1)
・UL Listed (File No.S24210) (※2)
・TheEMC level is in conformity with a requirements of ECE Regulation No. 10 standards. (EH□-M3 Only)

이 기기는 업무용 환경에서 사용할 목적으로 적합성평가를 받은 기기로서 가정용 환경에서 사용하는 경우 권과관심의 우려가 있습니다.

7-5 Outer Dimensions (mm)



NOTE

This device complies with part 15 of the FCC Rules.
Operation is subject to the following two conditions:
(1) This device may not cause harmful interference.
(2) This device must accept any interference received, including interference that may cause undersired operation.
This equipment has been tested and found to comply with the limits for a Class A digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference when the equipment is operated in a commercial environment.
This equipment generates, uses, and can radiate radio frequency energy and, if not installed and used in accordance with the instruction manual, may cause harmful interference to radio communications.
Operation of this equipment in a residential area is likely to cause harmful interference in which case the user will be required to correct the interference at his own expense.