




NOTE / 备注:


1.Electrical / 电气性能
1.1 Current Rate / 电流 : 2 A

2.Environmental / 环境
2.1 Operating temperature range / 工作温度 : -40℃ ~ 85℃

3.Mechanical / 机械性能
3.1 Working spring force / 弹力 : 125 ± 30%gf at 2.5mm (工作行程)
3.2 Working stroke / 行程 : 2.5 mm
3.3 Durability / 耐久性 : 10,000 cycles

4.Material / 材料
4.1 Plunger / 针头 :
Brass C3604,3u" gold plating over 80-240u Ni palting
4.2 Barrel / 针管 :
Brass C3604, 3u" gold plating over 80-240u Ni palting
4.3 Spring / 弹簧 : BeCu/铍铜, 1u" gold plating

5.General tolerance / 未注公差 : Unit:mm
.X. = ±0.30
.X = ±0.15
.XX = ±0.05

深圳市启华科实业有限公司			
Shenzhen QH Industrial Co.,Ltd			
E-mail / 邮箱: sales@pogopin-connectors.com			
Name	16.2mmH DIP POGO PIN	Spec	See NOTE
Part No.	101210001	Material	See NOTE
Drawing No.	101210001	Surface	See NOTE
View	Drawing	Yang	Date
	Scale	FiT	Date
	UOM	mm	fw
003			