

ISM 433 MHz Antenna SMA plug 2 dBi omnidirectional black roof mount outdoor

Description

This ISM antenna by Delock can be installed outdoors and can be used with the 433 MHz band.



Item no. 89487

EAN: 4043619894871

Country of origin: China

Package: Zip poly bag

Technical details

- Connector: SMA plug
- Frequency range: 433 MHz +/- 3 MHz
- Antenna gain: 2 dBi
- Impedance: 50 Ohm
- Polarisation: linear vertical
- VSWR: 2.0
- Operating temperature: -40 °C ~ 85 °C
- Protection class: IP67
- Screw mounting 13 mm central hole
- Thread length: 19.5 mm
- Thread: M12
- Colour: black
- Dimension: (L x Ø): ca. 75.5 x 45.2 mm
- Cable category: coaxial
- Cable type: RG-58 U
- Cable attenuation: 0.35 dB @ 400 MHz per meter
- Cable diameter: 4,95 mm
- Cable length incl. connector: ca. 2 m

System requirements

- Device with a free SMA jack

Package content

- ISM 433 MHz antenna
- Screw nut

Images



General

Mounting type:	Screw mounting with 13 mm bore hole
Protection class:	IP67
Suitable for indoor:	yes
Suitable for outdoor:	yes

Interface

Connector:	1 x SMA plug
------------	--------------

Technical characteristics

Frequency range:	433 MHz
Gain:	2 dBi
Impedance:	50 Ω
Operating temperature:	-40 °C ~ 85 °C
Polarisation:	linear vertical
Transmission power:	10 W
VSWR:	2.0

Physical characteristics

Housing colour:	black
Housing material:	ABS UV resistant
Thread length:	19.5 mm
Cable category:	coaxial
Cable type:	RG-58 U
Cable attenuation:	0.35 dB @ 400 MHz per meter RG-58 U
Cable colour:	black
Cable length incl. connectors:	2 m

Diameter:	45.2 mm
Height:	75.5 mm
Colour:	black
Thread type:	M12
Cable diameter:	4.95 mm RG-58 U

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

