






PACKING DRAW



PIN OUT



NOTE:

1. Electrical test:

- (1).100% open short & miss wire test;
- (2).Insulation resistance:DC 300V 10M ohm;
- (3).Contactor resistance:3 ohm;

2. RoHS COMPLIANT

3. PRINT WORD:E258105 兄 AWM STYLE 20276 80°C 30V VW-1 DVI

MATERIAL LIST:

⑦	DUST COVER	HDMI F Transparent LD-PE	2	pcs					
⑥	HDMI CONNECTOR	HDMI 19P/AF SOLDER Type, The Pin Gold Plating, the shell for Gold Plated	2	pcs					
⑤	DVI SCREW	Gold PLATED MATERIAL SCREW, Φ4.0mm*L:47mm, MOLDING BLACK, REACH COMPLIANT	2	pcs	DRAWING	WE0569	PART NAME	DVI (18+1) AM TO 2*HDMI 19/F	
④	OVER MOLDING	PVC 88A BLACK REACH COMPLIANT	2	pcs	CUSTOMER	WEC	ICON		
③	INNER MOLDING	LD-PE	2	pcs	CUSTOMER'S ITEM	68739	TOLERANCE		
②	DVI	DVI (18+1)/M SOLDER Type, The Pin Gold Plating, the shell for Gold Plated, black	1	pcs	APPRO BY	CHECK BY	DRAWN BY	SCALE	MM
①	CABLE	28AWG (18+1) (7/0.12BC*1P+E+WAM)*4+7/0.12BC*1P+7/0.12BC*3C+AEB B=0.12mm/7*16 AL-MG REACH COMPLIANT JACKET: PVC/BLACK OD: 7.3±0.2mm	1	pcs	Amy. zhang		Ada. ye	PAGE	1/1
NO.	PARTS NAME	SPECIFICATION DESCRIPTION	QT' Y	REMARK					