# Adapter USB 10 Gbps Type-A male to female, U-shaped

## Description

This USB adapter by Delock can be used for connection of USB devices.

### Space-saving

The U-shaped design routes the cable with a USB-A connector along the back of the device. This frees up more space for your device and makes it easier to keep cables organized without tangling.

### Port saver

The adapter can also be used as a port saver, safeguarding the USB interface in applications with frequent plug-in cycles.

### Fast charging and power

The USB adapter enables fast charging with its 60 W with a power bank or modern USB chargers. Quick Charge 3.0 is supported up to 20 V and 3 A.



**Item no. 67424**

EAN: 4043619674244

Country of origin: China

Package: Zip poly bag

## Technical details

- connectors:
  1 x USB 10 Gbps Type-A female
  1 x USB 10 Gbps Type-A male
- Fast Charging function: 20 V / 3 A (60 W)
- Data transfer rate up to 10 Gbps
- U form
- Colour: black
- Dimensions (LxWxH): ca. 23 x 18 x 15 mm

## Package content

- Delock poly bag

All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**

## Images







All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**

## General

| | |
|---|---|
| Specification: | USB 10 Gbps |

## Interface

| | |
|---|---|
| Connector 1: | 1 x USB Type-A female |
| Connector 2: | 1 x USB Type-A male |

## Technical characteristics

| | |
|---|---|
| Data transfer rate: | 10 Gbps |

## Physical characteristics

| | |
|---|---|
| Housing material: | Plastic |
| Length: | 23 mm |
| Width: | 18 mm |
| Height: | 15 mm |
| Colour: | black |

### Manufacturer information


| | |
|---|---|
| Street | Beeskowdamm 13/15 |
| Postal code | 14167 |
| City | Berlin |
| Country | Deutschland |
| E-Mail | info@delock.de |
| Website | www.delock.de |


All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**



All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**