


嘉尼企業股份有限公司 CANAL ELECTRONIC CO.,LTD.

SPECIFICATION MODEL : TB SERIES

Electrical Life : 10,000 cycles (cURus/ENEC15)
 Mechanical Life: 50,000 cycles
 Contact resistance: 20mΩ Initial (MAX),
 Insulation resistance: 500VDC - 100MΩ (MIN).
 Dielectric Strength:
 (1) 1500VAC For 1 minute (Terminal to Enclouse)
 (2) 500VAC For 1 minute (Terminal to Terminal)
 Rating & ingress protection: reference to table



#	Rating	IP
A	16(8)A 125/250~ T55	68
B	20(8)A 125/250~ T55	68
C	16A 6~30VDC T55	68
D	20A 6~30VDC T55	68
1	16(8)A 125/250~ T125/55	40
2	20(8)A 125/250~ T125/55	40
3	16A 6~30VDC T125/55	40
4	20A 6~30VDC T125/55	40

NOTE: TOLERANCES UNLESS OTHERWISE SPECIFIED : $\pm \begin{matrix} .02 \\ 0.5 \end{matrix}$ (mm).

REVISION	DESCRIPTION	REVISED BY	TOLERANCES X.X:		ANGLE $\frac{1}{2}^\circ$		UNIT	mm	PART NAME	SPEC DRAWING	DWG NO
④			DRAWN BY	范修銓	DESIGNED BY	范修銓	SCALE	1/1	PART NO	TB4-#B13-1	WS5245A
③			CHECKED BY	ERIC	APPROVED BY	范修銓	DATE	2022.12.15			
②	2022.12.15 首次出圖	范修銓									

