



Product: [4504FE](#)

Security & Sound, 6 Conductor 22 AWG BC, LSZH, Shielded, Eca

Product Description

Security & Commercial Audio Cable, 6-22 AWG stranded bare copper conductors with polypropylene insulation, Beldfoil® shield, LSZH jacket with ripcord, CPR Eca

Technical Specifications

Product Overview

Suitable Applications:	Security System, Intercom/PA, Audio/Speaker, Power-Limited Controls, Noisy Environment
------------------------	--

Physical Characteristics (Overall)

Conductor					
Element	AWG	Stranding	Material	Nominal Diameter	No. of Conductors
Conductor(s)	22	7x30	BC - Bare Copper	0.75 mm	6
Conductor Count:				6	

Insulation				
Type	Material	Nominal Diameter	Diameter +/- Tolerance	Nominal Wall Thickness
Insulation	PP - Polypropylene	1.07 mm	0.05 mm	0.2 mm

Color Chart	
Number	Color
Wire 1	Black
Wire 2	Red
Wire 3	White
Wire 4	Green
Wire 5	Brown
Wire 6	Blue

Outer Shield						
Type	Material	Material Trade Name	Coverage [%]	Thickness of Foil	Drainwire Material	Drainwire AWG
Tape	Bi-Laminate (Alum+Poly)	Beldfoil®	100%	9 µm	TC - Tinned Copper	AWG24/7

Outer Jacket			
Material	Nominal Diameter	Nominal Wall Thickness	Ripcord
LSZH - Low Smoke Zero Halogen (Flame Retardant)	4.4 mm	0.4 mm	Yes

Construction and Dimensions

Cabling
Description
6 wires twisted

Electrical Characteristics

Conductor DCR	
Nominal Conductor DCR	Nominal Outer Shield DCR

54 Ohm/km	50 Ohm/km
-----------	-----------

Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield
105 pF/m	185 pF/m

Current

Max. Recommended Current [A]
2 Amps per Conductor

Voltage

Voltage Rating [V]
300 V

Temperature Range

Installation Temperature Range:	-20°C To +70°C
Storage Temperature Range:	-30°C To +70°C
Operating Temperature Range:	-20°C To +70°C

Mechanical Characteristics

Bulk Cable Weight:	84 lbs/1000ft
Max. Pull Tension:	42 lbs
Min. Bend Radius During Installation:	44 mm
Min Setting Radius:	22 mm

Standards

CPR Euroclass:	Eca
----------------	-----

Applicable Environmental and Other Programs

Environmental Space:	Indoor - Euroclass Eca
----------------------	------------------------

Flammability, LSOH, Toxicity Testing

IEC Flammability:	IEC 60332-1-2
IEC 60754-1 - Halogen Amount:	Zero
IEC 60754-2 - Halogen Acid Gas Amount - Max. Conductivity:	2.5 µS/mm
IEC 60754-2 - Halogen Acid Gas Amount - Min. pH:	4.3
IEC 61034-2 - Smoke Density Min. Transmittance:	60%

Related Part Numbers

Variants

Item #	Color	Put-Up Type	Length	EAN
4504FE.00100	Gray	Reel	100 m	8719605007186
4504FE.00500	Gray	Reel	500 m	8719605007193

History

Update and Revision:	Revision Number: 0.439 Revision Date: 02-15-2024
----------------------	--

© 2024 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.