

Antenna Cable SMA plug to SMA jack LMR/CFD300 2 m low loss

Description

The antenna cable by Delock is suitable for connecting components of radio frequency technology.



Item no. 90461

EAN: 4043619904617

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x SMA plug >
 - 1 x SMA jack
- Impedance: 50 Ohm
- Cable type: LMR300
- Cable type: coaxial
- Cable attenuation: 0.31 dB @ 2 GHz per meter
- Cable diameter: ca. 7.50 mm
- Cable colour: black
- Smallest bending radius: 72 mm
- Length incl. connectors (L): ca. 2 m


System requirements

- Device with one free SMA port

Package content

- Antenna cable

Images



Interface

Connector 1:	1 x SMA plug
Connector 2:	1 x SMA jack

Technical characteristics

Impedance:	50 Ω
------------	-------------

Physical characteristics

Cable category:	coaxial
Cable type:	LMR300
Cable attenuation:	0.31 dB @ 2 GHz per meter
Cable colour:	black
Cable length incl. connectors:	2 m
Smallest bending radius:	72 mm
Cable diameter:	7.5 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

