

Fiber Optical Cable with metal armouring LC Duplex to LC Duplex Singlemode OS2 3 m

Description

This fiber optical cable by Delock can be used to connect different networking devices, e.g. a switch to a media converter.

With metal armouring

The robust fiber optical cables offer increased protection against damage and outer influences such as moisture, dust or damaging rodents. Despite the metal sheath, the cables remain bendable and flexible. The fiber optical cables are also characterised by their high tensile strength.



Item no. 87921

EAN: 4043619879212

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
1 x LC Duplex >
1 x LC Duplex
- Singlemode OS2 cable with metal armour
- Fibre: 9/125 µm
- Ceramic ferrule with dust protection
- Cable diameter: ca. 3 mm
- Operating temperature: -20 °C ~ 85 °C
- LSZH (halogen-free)
- Colour: blue
- Length incl. connectors: ca. 3 m

Package content

- Optical fiber cable

Images



General

Style:	both sides identical
--------	----------------------

Interface

Connector 1:	1 x LC Duplex
Connector 2:	1 x LC Duplex

Technical characteristics

Operating temperature:	-20 °C ~ 70 °C
------------------------	----------------

Physical characteristics

Material:	LSZH (halogen-free)
Length:	3 m
Colour:	blue
Cable diameter:	3 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

