



Directive 2002/95/EC
"RoHS"
Compliant

3	1	REAR SIDE	COPPER ALLOY	TIN PLATED
2	1	MATING SIDE	COPPER ALLOY	min. 30µin HARD GOLD over min. 50µin NICKEL
1	1	RETAINING RING	COPPER ALLOY	NICKEL PLATED
item	quantity	part description	material	plating
partlist				
THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH			tolerance	scale: 10:1
			ISO 2768-m	material: SEE PARTLIST
			dim. in mm	title:
			drawn: 19.02.2008 Sonnenberg	HIGH POWER CONTACT MALE PREMATING SOLDER PIN / d=2,6mm / 20A D-SUB COMBINATION
			appd. 19.02.2008 Mickenbecker	
			norm	
DO NOT ALTER CAD DRAWING BY HAND			d-old	dwg no: Inventor 10
			a Origin	13K1A2435
			rev. description date name	DIN-A3 sh: 1
			part no: 131C12129X	

CONEC

APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	