

Delock LTE Antenna SMA 3 dBi Omnidirectional Fixed Black Adhesive Mounting

Description

This LTE antenna can be installed indoors and can be used for reception of different LTE bands. It is completely Bluetooth, UMTS, GSM, WLAN 2.4 GHz, Z-Wave and ZigBee compatible.



Item no. 88987

EAN: 4043619889877

Country of origin: China

Package: Zip poly bag

Technical details

- Connector: SMA plug
- LTE Band 1-10/12-20/23/25-30/33-41/43/44
- Frequency range: 690-960 / 1710-2700 Mhz
- UMTS/GSM/Bluetooth/WLAN 2,4GHz/ZigBee/Z-Wave/DECT/SRD
- Gain: 3 dBi
- Impedance: 50 Ohm
- VSWR: 2.0:1 max.
- Cable category: coaxial cable
- Cable typ: RG-174
- Cable attenuation: 0.93 dB @ 800 MHz per meter
- Cable colour: black
- Cable length: ca. 3 m
- Operating temperature: -10°C ~ 55°C
- Body: ABS UV resistant
- Dimensions (LxWxH): ca. 115 x 22 x 5 mm


System requirements

- Device with free SMA connector

Package content

- LTE antenna

Images



General

Mounting type:	self adhesive
Suitable for indoor:	yes

Interface

Connector:	1 x SMA plug
------------	--------------

Technical characteristics

Frequency range:	1710 - 2700 MHz 690 - 960 MHz
Antenna gain:	3 dBi
Impedance:	50 Ω
Operating temperature:	-10 °C ~ 55 °C
VSWR:	2.0

Physical characteristics

Housing material:	ABS UV resistant
Cable category:	coaxial
Cable type:	RG-174
Cable attenuation:	1.5 dB @ 1.5 GHz per meter RG-174
Cable colour:	black
Cable length incl. connectors:	3 m
Width:	22.0 mm
Height:	5.0 mm
Smallest bending radius:	10.5 mm
Colour:	black
Cable diameter:	2.70 mm RG-174

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

