

DATA SHEET

SUNGMUN CODE : UADR-16S-TR(LG)
DESCRIPTION : ROTARY DIP SWITCH




SUNGMUN ELECTRONICS CO., LTD.

Address 301-302,Bucheon Technopark 345, Seokcheon-ro, Ojeong-gu
Bucheon-si, Gyeonggi-do, Korea
TEL. +82-32-328-1941~4
FAX +82-32-328-1945
E-mail sungmun@sungmun.co.kr
Website www.sungmun.com


REV. NO.	DATE	REVISION	DR	CH	APP
△					

SPECIFICATION



- 1. Rating : 25mA, DC 12V (Switching)
25mA, DC 24V (None-Switching)
- 2. Contact Resistance : 100mΩ Max
- 3. Insulation Resistance : 100MΩ Min at DC 250V
- 4. Operating Force : 700gf Max
- 5. Life cycle : 10,000 steps
- 6. Sealing : IP67 (Dust & Water proof)
- 7. Packing : 50pcs Tube / 600pcs Reel Packing



P.C.B DIMENSION (Top View)



ACTUATOR



Reel Coded					
	C	1	2	4	8
0	●				
1	●	●			
2	●		●		
3	●	●	●		
4	●			●	
5	●	●		●	
6	●		●		
7	●	●	●		
8	●				●
9	●	●			●
10	●		●		●
11	●	●		●	
12	●			●	●
13	●	●		●	●
14	●		●	●	●
15	●	●	●	●	●

16 P o s i t i o n

Din ISO-2768-1m				
Ranges	0.5-3	3-6	6-30	30-120
Tolerance	±0.1	±0.1	±0.2	±0.3

DRAW/DESIGNED	CHECKED	APPROVED	UNIT	SCALE	MODEL NO.	TITLE
H.S LEE	K.N KIM	W.J LEE	mm	N:S	UADR-16S	ROTARY DIP SWITCH
2023-09-18	2023-09-18	2023-09-18				
SUNGUMUN ELECTRONICS CO.,LTD			A4		DRAW NO.	REV.
					UADR-16SLGJ-01	01

1. Description:

This specification describes "10X10 slim size of Rotary Dip Switches" which is U&H series.

1-1 Operating / Storage Temperature Range : -40°C ~ +85°C

2. Rating:

2-1 None-Switching : 25 mA, DC 24V

2-2 Switching : 25 mA, DC 12V

3. Type of Actuation : Rotating

4. Electrical Characteristics

ITEM	DESCRIPTION	TEST CONDITIONS	REQUIREMENTS
4-1	Visual Examination	By visual examination check without any out pressure & testing.	There shall be no defects that affect the serviceability of the product.
4-2	Contact Resistance	① To be measured between the two terminals associated with each switch pole. ② Measurements shall be made with a 1kHz shall current contact resistance meter.	100mΩ max.
4-3	Insulation Resistance	250V DC, 1minute ±5seconds	100 MΩ min.
4-4	Dielectric withstanding Voltage	250V AC(50Hz or 60Hz)shall be applied between all the adjacent terminal and between the terminal and the frame for 1 minute.	There shall be no breakdown or flashover.

 SUNG MUN ELECTRONICS	“U/H” SERIES ROTARY DIP SWITCH SPECIFICATION (10X10)	Rev. 03 P : 2 / 4
--	---	------------------------------------

5. Mechanical Characteristics

ITEM	DESCRIPTION	TEST CONDITIONS	REQUIREMENTS
5-1	Operation Force	Operating direction shall be clockwise or counter clockwise direction	700gf•cm max
5-2	Operation Life	Measurements shall be made following the test set forth below: 1)150mA, 24V DC resistive load 2)Rate of operation: 15~20 cycles/ minute 3)Step of operation: 10,000 steps	1)As shown in item 4-3, 4-4 2)Contact Resistance: 200mΩ max


6. Environmental Characteristics

ITEM	DESCRIPTION	TEST CONDITIONS	REQUIREMENTS
6-1	Resistance Low Temperature	Following the test set forth below the sample shall be left in normal temperature and humidity conditions for an hour before measurements are made: 1)Temperature: -40°C ±3°C 2)Time: 96 hours	1)As shown in item 4-3, 4-4, 5-1 2)Contact Resistance: 200mΩ max
6-2	Resistance High Temperature	Following the test set forth below the sample shall be left in normal temperature and humidity conditions for an hour before measurements are made: 1)Temperature: 85°C ±2°C 2)Time: 96 hours	1)As shown in item 4-3, 4-4, 5-1 2)Contact Resistance: 200mΩ max
6-3	Resistance Humidity	Following the test set forth below the sample shall be left in normal temperature and humidity conditions for an hour before measurements are made: 1)Temperature: 40°C ±2°C 2)Relative humidity: 90~95% 3)Time: 96 hours	1)As shown in item 4-4, 5-1 2)Contact Resistance: 200mΩ max 3)Insulation Resistance: 10 MΩ min


7. This item is "RoHS" Compliant

8. Manual Soldering : Max 350°C, 3 sec.

9. Wave Soldering Conditions:



10. Reflow Soldering Conditions: (SMD type only)



10-1 Condition for Soldering

Profile Feature	Pb-Free Assembly
Average Ramp-UP Rate(Ts max to TP)	3°C/second max
Preheat - Temperature Min(Ts min) - Temperature Max(Ts max) - Time (ts min to ts max)	150°C 200°C 60-180seconds
Time maintained above: - Temperature (TL) - Time (tL)	217°C 60-150seconds
Peak/Classification Temperature(TP)	260°C +0°C/ -5°C
Time within 5°C of actual Peak Temperature(TP)	5~10 seconds
Ramp-Down Rate	6°C/sec max
Time 25°C to Peak Temperature	8 minutes max

