



# BRIGHTTEK

BRIGHTTEK (EUROPE) LIMITED

*Brighten up The World With LED!*



ISO/TS 16949:2009



BS EN ISO 14001:2004



QC 080000 IECQ HSPM

## PRODUCT DATASHEET




- ▶ CHIP LED Top View
- ▶ 0402 (1005) 0.50t
- ▶ Red 624nm

# NOR68S92



Release Date: 22 July 2026 Version: A1.1



### APPLICATIONS:

- Backlighting
- 3C Consumer Goods
- Indicator
- Light Strip

## 0402 (1005) 0.50t

**RoHS**  
Compliant



### FEATURES:

- **Package:** CHIP/PCB SMT Top View Package
- **Forward Current:** 20mA
- **Forward Voltage (typ.):** 2.0V
- **Luminous Intensity (typ.):** 112.5mcd@20mA
- **Colour:** Red
- **Dominant Wavelength (typ.):** 624nm
- **Viewing Angle:** X=120°; Y=128°
- **Materials:**
  - Resin: Epoxy (Water Clear)
- **Operating Temperature:** -40~+85°C
- **Storage Temperature:** -40~+100°C
- **Grouping Parameters:**
  - Forward Voltage
  - Luminous Intensity
  - Dominant Wavelength
- **Soldering Methods:** Reflow
- **MSL Level:** 2a according to J-STD020
- **Packing:** 8mm tape with max.4000pcs /reel, ø178mm (7")

## CHARACTERISTICS:

### Absolute Maximum Characteristics ( $T_a=25^{\circ}\text{C}$ )

| Parameter                                      | Symbol    | Ratings  | Unit               |
|------------------------------------------------|-----------|----------|--------------------|
| DC Forward Current                             | $I_F$     | 20       | mA                 |
| Pulse Forward Current<br>Duty Cycle 1/10, 1kHz | $I_{PF}$  | 100      | mA                 |
| Reverse Voltage                                | $V_R$     | 5        | V                  |
| Reverse Current @5V                            | $I_R$     | 10       | $\mu\text{A}$      |
| Power Dissipation                              | $P_D$     | 48       | mW                 |
| Operating Temperature                          | $T_{OPR}$ | -40~+85  | $^{\circ}\text{C}$ |
| Storage Temperature                            | $T_{STG}$ | -40~+100 | $^{\circ}\text{C}$ |


### Electrical & Optical Characteristics ( $T_a=25^{\circ}\text{C}$ )

| Parameter                    | Symbol          | Values |         |      | Unit | Test Condition    |
|------------------------------|-----------------|--------|---------|------|------|-------------------|
|                              |                 | Min.   | Typ.    | Max. |      |                   |
| Forward Voltage              | $V_F$           | ---    | 2.0     | 2.4  | V    | $I_F=20\text{mA}$ |
| Luminous Intensity           | $I_V$           | ---    | 112.5   | ---  | mcd  | $I_F=20\text{mA}$ |
| Dominant Wavelength          | $\lambda_D$     | ---    | 624     | ---  | nm   | $I_F=20\text{mA}$ |
| Peak Wavelength              | $\lambda_P$     | ---    | 632     | ---  | nm   | $I_F=20\text{mA}$ |
| Spectrum Radiation Bandwidth | $\Delta\lambda$ | ---    | 20      | ---  | nm   | $I_F=20\text{mA}$ |
| Viewing Angle (X/Y)          | $2\theta_{1/2}$ | ---    | 120/128 | ---  | deg  | $I_F=20\text{mA}$ |

1. Luminous intensity ( $I_V$ )  $\pm 10\%$ , Forward Voltage ( $V_F$ )  $\pm 0.1\text{V}$ , Viewing angle( $2\theta_{1/2}$ )  $\pm 5^{\circ}$


## OUTLINE DIMENSION:

### Package Dimension:



1. All dimensions are in millimetre (mm).
2. Tolerance  $\pm 0.13\text{mm}$ , unless otherwise noted.

### Recommended Soldering Pad Dimension:



1. Dimensions are in millimetre (mm).
2. Tolerance  $\pm 0.12\text{mm}$  with angle tolerance  $\pm 0.5^\circ$ .

## BINNING GROUPS:

---

Forward Voltage Classifications ( $I_F = 20\text{mA}$ ):

| Code | Min. | Max. | Unit |
|------|------|------|------|
| E18  | 1.6  | 2.4  | V    |

Luminous Intensity Classifications ( $I_F = 20\text{mA}$ ):


| Code | Min.  | Max.  | Unit |
|------|-------|-------|------|
| P    | 45.0  | 71.5  | mcd  |
| Q    | 71.5  | 112.5 |      |
| R    | 112.5 | 180.0 |      |
| S    | 180.0 | 285.0 |      |

Dominant Wavelength Classifications ( $I_F = 20\text{mA}$ ):


| Code | Min. | Max. | Unit |
|------|------|------|------|
| AD   | 615  | 635  | nm   |

## ELECTRO-OPTICAL CHARACTERISTICS:


Relative Luminous Intensity vs. Forward Current




Forward Current vs. Forward Voltage




Relative Spectral Power vs. Wavelength




Forward Current Derating Curve



Directive Radiation X




Directive Radiation Y





## RECOMMENDED SOLDERING PROFILE:

Reflow Lead-free Solder:




Note:

1. Maximum reflow soldering: 2 times.
2. The recommended reflow temperature is 240°C. The maximum soldering temperature should be limited to 260°C.
3. Before, during, and after soldering, should not apply stress on the components and PCB board.



## PACKING SPECIFICATION:

Reel Dimension:



## PRECAUTIONS OF USE:

---

### Storage:

It is recommended to store the products in the following conditions:

- Humidity: 60% R.H. Max.
- Temperature: 5°C~30°C (41°F ~86°F).

Shelf life in sealed bag: 12 months at 5°C~30°C and <60% R.H.

Once the package is opened, the products should be used within 4 weeks. Otherwise, they should be kept in a damp-proof box with descanting agent <10% R.H. and apply baking before use.

### Baking:

It is recommended to bake the LED before soldering if the pack has been unsealed for longer than 24hrs. The suggested baking conditions are as followings:

- 60±3°C x 12hrs and <5%RH, taped / reel package.

It's normal to see slight color fading of carrier (light yellow) after baking in process.

### Testing Circuit:



Must apply resistor(s) for protection (over current proof).

### Cleaning:

Use alcohol-based cleaning solvents such as isopropyl alcohol to clean the LED carrier / package. Avoid putting any stress force directly on to the LED lens.

### ESD (Electrostatic Discharge):

Static Electricity or power surge will damage the LED. Use of a conductive wrist band or anti-electrosatic glove is recommended when handling the LED all time. All devices, equipment, machinery, work tables, and storage racks must be properly grounded.

In the events of manual working in process, make sure the devices are well protected from ESD at any time.

**REVISION RECORD:**

---

| Version | Date       | Summary of Revision         |
|---------|------------|-----------------------------|
| A1.0    | 25/06/2026 | Datasheet set-up.           |
| A1.1    | 22/07/2026 | Revise pulse current value. |