



Figure similar

SIMATIC, terminal module TM-IM/EM60S for ET200iSP, for holding the IM152-1 and an electronic module, screw terminals, incl. power bus termination module, Ex eb [ia Ga/ib] IIC T4 Gb, Ex eb [ia IIIC Da] IIC T4 Gb, Ex eb [ia/ib] I Mb

General information	
Product type designation	TM-IM/EM60S
Product version	Screw terminals
Installation type/mounting	
Rack mounting	No
Front mounting	Yes
Rail mounting	Yes
Wall mounting/direct mounting	No
Supply voltage	
Type of supply voltage	DC
permissible range, lower limit (DC)	20.4 V
permissible range, upper limit (DC)	28.8 V
Input current	
At DC, max.	4 A
Output voltage	
Type of output voltage	DC
permissible range, lower limit (DC)	20.4 V
permissible range, upper limit (DC)	28.8 V
Output current	
At DC, max.	4 A
Hardware configuration	
Slots	
• Number of slots	2
• Plug-in modules, analog I/O	Yes
• Plug-in modules, digital I/O	Yes
• Plug-in modules, function modules and technology modules	No
• Plug-in modules, communication modules	No
• Plug-in modules, CPUs	Yes
• Plug-in modules, others	Yes
Standards, approvals, certificates	
CE mark	CE 0344
UKCA mark	DEKRA 21UKEX0032 Importer UK: Siemens plc Manchester M20 2UR
cULus	LISTED E334384
FM approval	CLASSIFIED 3025852
Suitable for safety functions	Yes
INMETRO certificate	UL-BR 12.0077
reference designation according to IEC 81346-2 (2009)	XX

Use in hazardous areas	
• ATEX marking • ATEX certificate • IECEx • CCC Ex • Explosion protection category for gas • Explosion protection category for dust • associated equipment (Ex ia) • associated equipment (Ex ib)	II 2 G (1) G Ex eb [ia Ga/ib] IIC T4 Gb II 2 G (1) D Ex eb [ia IIIC Da] IIC T4 Gb I M2 Ex eb [ia/ib] I Mb KEMA 04 ATEX 2242 IECEx KEM 05.0003 2020322310002881 ATEX gas explosion protection, Zone 1 ATEX dust explosion protection, Zone 21 always install in corresponding enclosure Yes Yes

Marine approval	
• Germanischer Lloyd (GL) • American Bureau of Shipping (ABS) • Bureau Veritas (BV) • Det Norske Veritas (DNV)	Yes Yes Yes Yes

Dimensions	
Width	60 mm
Height	190 mm
Depth	52 mm

Weights	
Weight, approx.	235 g

Classifications			
		Version	Classification
	eClass	16	27-24-26-03
	eClass	14	27-24-26-03
	eClass	12	27-24-26-03
	eClass	9.1	27-24-26-03
	eClass	9	27-24-26-03
	eClass	8	27-24-26-03
	eClass	7.1	27-24-26-03
	eClass	6	27-24-26-03
	ETIM	10	EC001598
	ETIM	9	EC001598
	ETIM	8	EC001598
	ETIM	7	EC001598
	IDEA	4	3560
	UNSPSC	15	32-15-17-04

Approvals / Certificates

General Product Approval



[Miscellaneous](#)



[China RoHS](#)

General Product Approval

For use in hazardous locations

[Manufacturer Declaration](#)



[FM](#)



[Miscellaneous](#)

For use in hazardous locations



[CCC-Ex](#)



[Miscellaneous](#)



For use in hazard-
ous locations

Maritime application



Environment



last modified:

4/28/2025