

STANDARD CABLE TIE BLACK

ITEM CODE	SIZE	COLOR	MAX Ø mm	TENSILE STRENGTH (N)
FIX-2.5x100-ST/BK	2,5x100	black	22	80
FIX-2.5x150-ST/BK	2,5x150	black	35	80
FIX-2.5x200-ST/BK	2,5x200	black	50	80
FIX-2.5x250-ST/BK	2,5x250	black	65	80
FIX-3.6x150-ST/BK	3,6x150	black	35	178
FIX-3.6x200-ST/BK	3,6x200	black	50	178
FIX-3.6x250-ST/BK	3,6x250	black	65	178
FIX-3.6x300-ST/BK	3,6x300	black	80	178
FIX-3.6x370-ST/BK	3,6x370	black	100	178
FIX-4.6x200-ST/BK	4,6x200	black	50	216
FIX-4.6x250-ST/BK	4,6x250	black	65	216
FIX-4.6x300-ST/BK	4,6x300	black	80	216
FIX-4.6x350-ST/BK	4,6x350	black	90	216
FIX-4.6x400-ST/BK	4,6x400	black	105	216
FIX-4.6x450-ST/BK	4,6x450	black	120	216
FIX-4.6x500-ST/BK	4,6x500	black	150	216
FIX-7.6x300-ST/BK	7,6x300	black	80	540
FIX-7.6x400-ST/BK	7,6x400	black	105	540
FIX-7.6x500-ST/BK	7,6x500	black	150	540
FIX-8.8x650-ST/BK	8,8x650	black	190	981
FIX-8.8x760-ST/BK	8,8x760	black	225	981

Parameter

Installation Temperature

Working Temperature

Moisture Absorption

Material Fire Resistance (UL 94)

Resistance to

Resistant

Limited Resistance

Non-Resistant

Material

Specification

-10°C to +60°C

-40°C to +85°C

2.7% (23°C; 50% R.H.)

V-2; halogen-free

aromatic solvents, oils, greases, and their derivatives

ultraviolet exposure

acids

phenols and chlorinated solvents

polyamide 6.6 + 1% carbon black

