

433 MHz Antenna N plug 1.45 dBi omnidirectional fixed outdoor white

Description

This antenna by Delock allows the usage of the 433 MHz band outdoors.



Item no. 89638

EAN: 4043619896387

Country of origin: Taiwan,
Republic of China

Package: Retail Box

Technical details

- Connector: 1 x N plug
- Frequency range: 433 MHz
- Antenna gain: 1.45 dBi
- Impedance: 50 Ohm
- Efficiency: 51.46 %
- VSWR: 2.5
- Polarisation: vertical
- Antenna type: rod antenna
- Operating temperature: -40 °C ~ 70 °C
- Housing material: ABS
- Colour: white
- Dimensions (LxD): ca. 187 x 23 mm
- Thread diameter: ca. 20 mm


System requirements

- Device with a free N jack

Package content

- Antenna

Images



General

Suitable for indoor:	yes
Suitable for outdoor:	yes

Interface

Connector:	1 x N male
------------	------------

Technical characteristics

Frequency range:	433 MHz
Antenna gain:	1.45 dBi
Impedance:	50 Ω
Operating temperature:	-40 °C ~ 70 °C
VSWR:	2.5
Efficiency:	51.46 %

Physical characteristics

Antenna type:	Rod antenna
Housing material:	ABS
Diameter:	22.8 mm
Length:	187 mm
Diameter connector:	20 mm
Colour:	white

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

