

Model	Item Code	Output current	Input current	Input power	Output power range	PF	Efficiency	Output voltage	No load voltage
CC23W100-700-0-10-NX	157840	100mA	0.04A	5.40W	0.30-4.20W	0.67	77.7%	2.5-42V	65V Max.
		150mA	0.05A	7.70W	0.40-6.30W	0.80	81.5%		
		200mA	0.06A	10.00W	0.50-8.40W	0.85	84.1%		
		250mA	0.07A	12.30W	0.60-10.50W	0.88	85.4%		
		300mA	0.08A	14.60W	0.80-12.60W	0.92	86.4%		
		350mA	0.09A	16.90W	0.90-14.70W	0.93	87.1%		
		400mA	0.10A	19.20W	1.00-16.80W	0.94	87.6%		
		450mA	0.11A	21.40W	1.10-18.90W	0.95	88.3%		
		500mA	0.12A	23.80W	1.30-21.00W	0.96	88.2%	2.5-40V	
		550mA	0.12A	24.90W	1.40-22.00W	0.96	88.2%	2.5-38V	
		600mA	0.12A	25.90W	1.50-22.80W	0.96	88.0%	2.5-35V	
		650mA	0.12A	26.00W	1.60-22.80W	0.96	87.6%	2.5-32V	
		700mA	0.12A	25.60W	1.80-22.40W	0.96	87.3%	2.5-32V	

*** Test result @230V, 50Hz, Full Load.**

1. Parameters

Category	Item	Technical Norm
Features	Output Type	Constant Current
	Dimming range	0/10%-100%
	Output Features	Isolation
	IP Grade	IP20
	Insulation Class	Class II

Input	Rated Input Voltage	220-240VAC
	Range of Input Voltage	198-264VAC
	Range of DC Input Voltage	180-280VDC
	Frequency	0/50/60Hz, Range:0/47-63Hz
	Overvoltage protection	2h@380VAC, 48h@320VAC
	Input Current	≤0.12A
	Input Power	≤25.60W (230VAC , full load)
	Power Factor	≥0.96 (230VAC , full load)
	THD	≤ 11% (230VAC , full load)
	No-load Power Consumption	≤0.5W (230VAC , full load)
	Inrush Current	≤7.9A/16us (230VAC, full load)
	Connected quantity of 10A Breaker	24pcs/type A ; 39pcs/type B ; 63pcs/type C
	Connected quantity of 13A Breaker	32pcs/type A; 51pcs/type B ; 82pcs/type C
	Connected quantity of 16A Breaker	39pcs/type A; 63pcs/type B ; 101pcs/type C
	Connected quantity of 20A Breaker	49pcs/type A; 79pcs/type B ; 126pcs/type C
Output	Output Voltage Range	2.5-42VDC@100-500mA, 2.5-40VDC@550mA, 2.5-38VDC@600mA, 2.5-35VDC@650mA, 2.5-32VDC@700mA
	No Load Voltage	65VDC Max.
	Output Current	100-700mA (Factory set current of 100mA)
	Max. Output Power	22.8W
	Efficiency	≥88.3 % @450mA, 230VAC
	Output LF current ripple (< 120 Hz)	±3% (Imax-Imin) / (Imax+Imin)
	Current Accuracy	±5%
	PSTLM	≤1
	SVM	≤0.4
	Starting Time (AC mode)	≤0.5S (230VAC , full load)
Protection	Short Circuit Protection	Auto Recovery
	Overload Protection	Auto Recovery (not be hot swap)
	No-load Protection	Auto Recovery
	Insulation voltage	3000V 5mA 60S between P-S
	Insulation resistance	>100M ohm @ 500VDC
	Leakage current	<700μA,I/P to O/P @230V input
Environment	Ta/Operation Temperature	-20....+50℃
	Ts/Storage Temperature	-20....+85℃
	Tc/Enclosure Temperature	85℃
	Humidity	10%.... 90%RH
	Atmosphere	86-108KPa
Construction	Connection Method	Push-in Terminal
	Installation	Build-in & Independent
	PRI Wire preparation	0.5-1.5□/ 8-9mm
	SEC Wire preparation	0.5-1.5□/ 8-9mm


	SEC Wire preparation	0-0.8±0.05m (The EMC test results were achieved at approximately 0.8 meters) (the length required by the standard). If there are any data differences, please test according to the length required by the standard)
	Dimension	103.4 *30*21mm (L*W*H)
Standards	Certification	CE
	Safety Standards	EN61347-1:2015/A1:2021; EN61347-2-13:2014/A1:2017;
	Performance	EN62384
	Surge	L/N-Ground:2kV; L-N:1kV
Others	RoHS	complied to 2011/65/EU
	Life Time	50000h Tc=85°C
		75000h Tc=80°C
		100000h Tc=75°C
	Warranty	5years , F.R. < 10000ppm

Remark:

- 1.All Parameters,if not specified,are measured at 230VAC/50Hz and 25°C ambient temperature.
- 2.LED Driver is a component of the luminaires. Luminaires and wire layout will affect the EMC, please check the EMC with end products again.

Distance	15m	30m	50m
Cable selection	0.5mm ²	0.75mm ²	1.0mm ²

2. Label




3. Output current setting

Output Current	1	2	3	4
100mA	-	-	-	-
150mA	-	-	-	ON
200mA	-	-	ON	-
250mA	-	-	ON	ON
300mA	-	ON	-	-
350mA	-	ON	-	ON
400mA	-	ON	ON	-
450mA	-	ON	ON	ON
500mA	ON	-	-	-
550mA	ON	-	-	ON
600mA	ON	-	ON	-
650mA	ON	-	ON	ON
700mA	ON	ON	-	-


4. Dimension (Unit: mm)

Built in type:




Compatible Small Strain reliefs:SR_CC_15-23-36_UNI
Compatible Large Strain reliefs:SR_CC_15-23-36_5POL




Strain reliefs



Large Strain reliefs



Large Strain reliefs specifications



Tolerance for dimensions ± 0.1 mm

Mechanical, Operating & Storage Conditions

Driver cross-section dimensions: 55.4-57.4 x 20.0-22.0 mm

Wire size: 0.5 - 2.5 mm²

Ambient temperature range: -20...+50 °C

Storage temperature range: -20...+85 °C


Assembly temperature range: +5...+30 °C

Do not store in wet or humid environment!



*Unless otherwise stated in the driver datasheet (for independent installation).

Note! Tc max temperature of the driver shall not be exceeded.

Terminal




5 - pole connector for DA / CC drivers with LC-SRB-LOOP




5. Wiring Diagram

220-240 V
0/50/60 Hz




6. 0-10V Dimming Current curve (DIP setup output current @ 100mA)




7. Electrical values

1. Operating power windows




8. Packing information

Built-in type



Carton L*W*H(mm)	Pcs/Carton	Net weight/ Pcs(kg)	Net weight/ Carton(kg)	Gross weight / Carton(kg)
398*230*130	130	0.072	9.38	9.88

Small Strain reliefs




Inner box

Carton L*W*H(mm)	Pcs/Carton	Net weight/ Pcs(kg)	Net weight/ Carton(kg)	Gross weight / Carton(kg)
180*118*75	50	0.007	0.36	0.47

Outer box

Carton L*W*H(mm)	Pcs/Carton	Net weight/ Pcs(kg)	Net weight/ Carton(kg)	Gross weight / Carton(kg)
500*195*245	600	0.007	4.26	5.56

Large Strain reliefs



Inner box

Carton L*W*H(mm)	Pcs/Carton	Net weight/ Pcs(kg)	Net weight/ Carton(kg)	Gross weight / Carton(kg)
300*180*122	44	0.055	2.42	2.77

Outer box

Carton L*W*H(mm)	Pcs/Carton	Net weight/ Pcs(kg)	Net weight/ Carton(kg)	Gross weight / Carton(kg)
375*315*385	264	0.055	14.52	16.16

9. Ordering Data

Model No	Item code
CC23W100-700-0-10-NX	157840
SR_CC_15-23-36_UNI	147841
SR_CC_15-23-36_5POL	147851

10. REVISION HISTORY

Date	Revision	Remark
2026.16.03	V0.01	Product release
2026.27.06	V0.02	Add the logo for applying for ENEC certification
2026.17.07	V0.03	Label, update images