




Rating	16(6)A 125/250VAC 25A 14VDC,15A 28VDC	Mounting Hole 	Circuit Diagram 											
Contact Resistance	50m ohm Max.													
Insulation Resistance	DC 500V 100M ohm Min.													
Dielectric Strength	AC 1500V 1 minute													
Operation Temperature	-25°C~85°C													
Switch Function	2P SPST ON-OFF	<table><tr><td>Thickness</td><td>X</td><td>Y</td></tr><tr><td>0.75...2.5</td><td>27.6-0.1</td><td>13.8+0.1</td></tr><tr><td>2.5...3.5</td><td>27.8-0.1</td><td>13.8+0.1</td></tr><tr><td>3.5...4.5</td><td>28.0-0.1</td><td>13.8+0.1</td></tr></table>	Thickness	X	Y	0.75...2.5	27.6-0.1	13.8+0.1	2.5...3.5	27.8-0.1	13.8+0.1	3.5...4.5	28.0-0.1	13.8+0.1
Thickness	X	Y												
0.75...2.5	27.6-0.1	13.8+0.1												
2.5...3.5	27.8-0.1	13.8+0.1												
3.5...4.5	28.0-0.1	13.8+0.1												



MATERIAL:

Frame: Black, Nylon#66





Actuator: Black, Nylon#66+30%GF

Waterproof rubber: Black, Silicone

Terminals: Silver plated, Copper alloy

Printed: White, hot stamping

IP Rating: IP65



Tolerances $\pm 0.3\text{mm}$ Unless Otherwise Specified

06/19/14	黃洋	增加SCI LOGO,更新圖面				△
Date	Name	Description				△
Drawn	Checked	Approved	SCI BOM No.	1824432	Model Name	ROCKER SWITCH
黃洋	周木輝		Customer No.		Model No.	R13-238A8-01
06/19/14	6/20-14	6/24-14	Unit	mm	Shin Chin Industrial Co., Ltd.	
						Rev. 1