

AM/FM ANTENNA WITH DAB READY ROD

GENERAL DESCRIPTION


AM/FM antenna with rod prepared to receive the DAB digital radio signals.

The unique design and materials makes the rod very flexible and resistant to high mechanical stress present in difficult work environment as agricultural and construction vehicles.




DIMENSIONS


Antenna



Flexible rod details



Extension cable



TECHNICAL DATA

Antenna type	Passive
Frequencies	AM: 525 - 1710 kHz FM: 87,5 - 108 MHz DAB: 174 - 240 MHz
Base inclination	0 ÷ 180°
Rod type	Smooth
Rod lenght	240 mm
Rod thread	M6
Cable type	RG58
Cable lenght	2500 mm
Cable connector	DIN Male
Impedance	50 Ω
Mounting position	Roof, pillar and fender
Mounting surface	Metal surface
Coachwork drilling	Round Ø 9 mm
IP grade	IP68
DAB reception	To enable the DAB reception an optional active or passive splitter is needed

DISCLAIMER – Products, information, drawings, specifications and reference numbers (hereafter “contents”) discussed herein are for reference purposes only. All contents herein are provided on an “as is” basis, without warranties of any kind. The contents discussed herein remain the sole and exclusive property of MTA S.p.A. and shall not be copied, translated in whole or in part without MTA S.p.A. prior written consent. No license of any patent, copyright, mask work, trademark or any other intellectual property right is granted under this document, by implication, estoppel or otherwise. Contents may be modified and changed by MTA S.p.A. without any notice. For updates or additional information about MTA products, please contact your nearest MTA office. All brand names, trademarks and registered trademarks belong to their respective owners.