





The color of lever is consistent with body's



△△ N = Number of poles

Dim L=(N×2.5)+1.5

Dim P=(N-1)×2.5

|         | Dim L | Dim P |
|---------|-------|-------|
| 2p-8p   | ±0.20 |       |
| 10p-12p | ±0.30 |       |
| 14p-18p | ±0.40 |       |
| 20p-24p | ±0.50 |       |

HC xx B 0 x 0 xxxx G △△ RoHs compliant (lead<4%) In copper Alloy

△ NO of poles  
02 2 poles  
04 4 poles  
... ..  
24 24 poles

△ Body Color  
0 Black (RAL9005)  
2 Red (RAL3001/D)  
3 Orange(RAL2011/P)  
4 Yellow(RAL1018/A)  
5 Green(RAL6018/T)  
6 Blue (RAL5015/A)  
8 Grey(RAL7004/P)  
9 White(RAL1102)  
C Multiple colors

0000: "△" Logo (Standard)  
000A: "ANYTEK" Mark  
Any special item by customer request.  
please contact sales department.

**ANYTEK**

**CUSTOMER COPY**

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

|          |               |                                                                             |                        |          |            |
|----------|---------------|-----------------------------------------------------------------------------|------------------------|----------|------------|
| TITLE    |               | HC 2.5mm Series (Double row center contact link together with end cover) 雙聯 |                        |          |            |
| PART NO. | HCxxB0x0xxxxG |                                                                             |                        | DWG NO.  | 8HC0302    |
| APPROVED | CHECKED       | DESIGNED                                                                    | DRAWN                  | CUST NO. |            |
|          |               | Da cheng<br>2013.12.28                                                      | Da cheng<br>2013.12.28 |          | Tolerance  |
|          |               |                                                                             |                        |          | X. ±0.50   |
|          |               |                                                                             |                        |          | X.X ±0.30  |
|          |               |                                                                             |                        |          | X.XX ±0.10 |
|          |               |                                                                             |                        |          | X° ±1°     |

Material:

- Item ① Insulator(lever): Thermoplastic (UL94V-0)
- Item ② Insulator(housing): Thermoplastic (UL94V-0)
- Item ③ Side contact pin: PhBz.Tin plated.
- Item ④ Center contact pin: PhBz.Tin plated.
- Item ⑤ Side Cover : Thermoplastic (UL94V-0)

|                                |                  |        |                        |
|--------------------------------|------------------|--------|------------------------|
| △ Electrical:                  | cULus            | CQC    | TUV △                  |
| △ ● Voltage rating:            | 300V             | 300V   | 150V                   |
| ● Current rating:              | 2A               | 2A     | 2A                     |
| ● Wire range:                  |                  |        | 0.2~0.5mm <sup>2</sup> |
| ● Solid wire(AWG):             | 20-26            | 20     |                        |
| ● Stranded wire(AWG):          | 20-26            | 20     |                        |
| △ ● Wire strip length:         | 8.5-10.0mm       |        |                        |
| ● Withstanding Voltage:        | 1.6KV            | 2.5KV  | 2.5KV                  |
| △ ● Operating temperature:     | -40°C            | +115°C |                        |
| △ ● The soldering temperature: | 260°C±5°C/5 Sec. |        |                        |
| △ △ ● Safety Approval:         |                  |        |                        |
| △ ● Critical dimension:        |                  |        |                        |