

WiFi 2.4 GHz Antenna RP-SMA plug 7 dBi omnidirectional with tilt joint black

Description

This Wireless LAN antenna by Delock can be connected to a WLAN device with RP-SMA interface, in order to send and receive signals.



Item no. 90763

EAN: 4043619907632

Country of origin: China

Package: Box

Technical details

- Connectors: 1 x RP-SMA plug
- Frequency range: 2.400 - 2.500 GHz
- Antenna gain: 7 dBi
- Impedance: 50 Ohm
- Operating temperature: -40 °C ~ 60 °C
- Housing material: TPE
- Colour: black
- Dimensions (LxD): ca. 290 x 13 mm


System requirements

- Device with a free RP-SMA jack

Package content

- WLAN antenna

Images



General

Mounting type:	Screw mounting
Suitable for indoor:	yes

Interface

Connector:	1 x RP-SMA plug
------------	-----------------

Technical characteristics

Frequency range:	2400 - 2500 MHz
Antenna gain:	7 dBi
Impedance:	50 Ω
Operating temperature:	-40 °C ~ 60 °C
Polarisation:	vertical
Transmission power:	max. 50 W
VSWR:	< 2.5

Physical characteristics

Antenna type:	omnidirectional
Diameter:	13 mm
Length with tilt joint:	290 mm
Length without tilt joint:	270 mm
Colour:	black

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

