

PRODUCT DATASHEET

FL 10 P 8W 1K2LM 830 PS SY100 BK

FLOODLIGHT 10 | Versatile floodlight with up to 1200 lm light output



PERFOR-
MANCE
CLASS

Areas of application

- Replacement for floodlights with halogen lamps
- Outdoor use (IP66)
- D-sign according to EN 60598-2-24 for fire-risk commercial unit, e.g. by accumulation of dust
- Public areas
- Building facades
- Construction areas
- Parking
- Gardens and balconies

Product benefits

- Breather membrane to optimize air exchange, without compromising IP protection
- Highly versatile due to selectable power steps (Multi Lumen) on the housing
- Robust cable gland with integrated waterstop function
- Safe and very uniform illumination, due to frosted and tempered glass diffuser
- Bright, robust and durable
- Energy savings of up to 90 % compared to halogen lamp floodlights
- No upper light output ratio (ULOR 0%) when mounted at 0° tilt

Product features

- High luminous efficacy: up to 145 lm/W
- Type of protection: IP66
- Pre-installed, flexible 1 m cable (H05RN-F), wrapped 3 x 1.0 mm² single wires
- Reflector-based, symmetric light distribution with 100° x 100° beam angle
- Mounting bracket with 30° angle and wide rotation area


TECHNICAL DATA

Electrical data


Nominal wattage	8 W / 6 W
Nominal voltage	220...240 V
Mains frequency	50...60 Hz
Nominal current	40/30 mA
Inrush current	7.64 A
Inrush current time T_{h50}	19.6 μ s
Max. number of luminaires per miniature circuit breaker B16	98
Max. number of luminaires per miniature circuit breaker C10	78
Max. number of luminaires per miniature circuit breaker C16	125
Power factor λ	> 0.90
Total harmonic distortion	< 20 %
Protection class	I
Surge capability (L-N)	2 kV
Surge capability (L/N-Ground)	4 kV
Operating mode	Integrated LED driver

Photometrical data

Luminous flux	1100 lm / 780 lm
Luminous efficacy	133 lm/W
Color temperature	3000 K
Light color (designation)	Warm White
Color rendering index Ra	80
Standard deviation of color matching	5 sdc _m
Stroboscope effect metric (SVM)	≤0.9
Photobiological safety group acc. to EN62778	RG1
Photobiological safety group acc. to EN62471	RG1
Beam angle	100 ° x 100 °




FL 10 P 8W 1K2LM 830 PS SY100 BK



FL 10 P 8W 1K2LM 830 PS SY100 BK

Dimensions & Weight

Length	136.00 mm
Width	36.00 mm
Height	127.00 mm
Product weight	420.00 g
Cable length	1000 mm



FL 10 P SY100

Materials & Colors

Product color	Black
Housing color	Black

RAL Color (most similar)	RAL 9017
Body material	Aluminum
Cover material	Glass
Light emitting surface material	Glass
Glow Wire Test according to IEC 60695-2-12	650 °C
Mercury content	0.0 mg

Application & Mounting

Ambient temperature range	-30...+50 °C
Temperature range at storage	-40...+70 °C
Type of connection	Cable, 3-pole
Type of protection	IP66
Protection class IK (shock resistance)	IK07
Corrosion resistance class acc. to EN 12944	C4
Dimmable	No
Mounting type	Surface
Mounting location	Wall / Ceiling / Floor
Application environment	Outdoor
Adjustable	Yes
With light source	Yes
Replaceable light source	No

Lifespan

Lifespan L70/B50 at 25 °C	100000 h ¹⁾
Lifespan L80/B10 at 25 °C	75000 h ¹⁾
Lifespan L80/B50 at 25 °C	70000 h
Lifespan L90/B10 at 25 °C	35000 h

¹⁾ t[h]: L70 / B50 @ 25 °C (Ta), t[h]: L80 / B10 @ 25 °C (Ta), t[h]: L90 / B10 @ 25 °C (Ta)

Control gear

Output current	68 mA
ECG - Output ripple current	< 20 %

Certificates & Standards

Standards	CE / CB / ENEC / EAC / UKCA / EPD
Luminaire with limited surface temperature, "D sign"	Yes
Ball shot safe	No
EPD	LEDV-00031-V01.01-EN

Additional product data

Added function

MULTI SELECT

Safety advice


– Max. wind load surface 0.012 m²

DOWNLOAD DATA

Documents and certificates		Document name
	User instruction / safety instructions	G11193706_UI_Floodlight_08W-41W
	Legal information	Insert_LSI_Floodlight_8_41w_G11195967
	Legal information	Informationstext 18 Abs 4 ElektroG
	Legal information	Safety Insert G11205496
	Legal information	Legal Insert G11257402
	Declarations of conformity	FLOODLIGHT GEN4
	Declarations of conformity UKCA	FLOODLIGHT GEN4
Photometric and lighting design files		Document name
	IES file (IES)	FL 10 P 8W 1K2LM 830 PS SY100 BK
	LDT file (Eulumdat)	FL 10 P 8W 1K2LM 830 PS SY100 BK
	ULD file (DIALux)	FL 10 P 8W 1K2LM 830 PS SY100 BK
	ROLF file (RELUX)	FL 10 P 8W 1K2LM 830 PS SY100 BK
	UGR file (UGR table)	FL 10 P 8W 1K2LM 830 PS SY100 BK
	Light distribution curve type cone	FL 10 P 8W 1K2LM 830 PS SY100 BK
	Light distribution curve type polar	FL 10 P 8W 1K2LM 830 PS SY100 BK
CAD/BIM files		Document name
	BIM Revit 3D	Floodlight G4

Product code	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Gross weight	Volume
4099854305689	Folding box 1	62 mm x 143 mm x 138 mm	471.00 g	1.22 dm³
4099854305696	Shipping box 12	390 mm x 300 mm x 163 mm	6144.00 g	19.07 dm³

ADDITIONAL CATALOG INFORMATION



		
FL 10 P 00W 10CLM 000 PS SY100	0.00 / 780 hrs	0.00 / 1100 hrs
FL 10 P 00W 10CLM 000 PS SY100	0.00 / 800 hrs	0.00 / 1200 hrs
FL 10 P 00W 10CLM 000 PS SY100	0.00 / 800 hrs	0.00 / 1200 hrs
FL 20 P 17W 00CLM 040 PS SY100	11.00 / 1400 hrs	10.00 / 2200 hrs
FL 20 P 17W 00CLM 040 PS SY100	11.00 / 1400 hrs	11.00 / 2300 hrs
FL 20 P 17W 00CLM 040 PS SY100	11.00 / 1400 hrs	11.00 / 2400 hrs
FL 50 P 41W 00CLM 030 PS SY100	27.00 / 3670 hrs	40.00 / 5000 hrs
FL 50 P 41W 00CLM 030 PS SY100	27.00 / 3670 hrs	40.00 / 5000 hrs
FL 50 P 41W 00CLM 030 PS SY100	27.00 / 3670 hrs	40.00 / 5000 hrs

– For Guarantee see www.ledvance.com/guarantee

© 2025, LEDVANCE GmbH. All rights reserved.