


PRO ECO 240W 24V 10A II SI
Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

SNAP IN 


The new PROeco 2nd generation power supplies maximise the availability of automation applications. The twelve-part series offers standard functions: with high performance, efficiency and suitability for many systems. The three-colour LED makes service activities and the integration of PROeco devices particularly easy. The series is compatible with DC UPS, electronic load monitoring and diode modules and is suitable for setting up power management systems. The compact design suits space-constrained applications, such as flat control cabinets in the field.

General ordering data

Version	Power supply, switch-mode power supply unit, 24 V
Order No.	3146470000
Type	PRO ECO 240W 24V 10A II SI
GTIN (EAN)	4099987579414
Qty.	1 items

PRO ECO 240W 24V 10A II SI

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate No. (cURus) E255651

Certificate no. (cULus) E258476

Dimensions and weights

Depth	100 mm	Depth (inches)	3.937 inch
Height	130 mm	Height (inches)	5.1181 inch
Width	52 mm	Width (inches)	2.0472 inch
Net weight	695 g		

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-25 °C...70 °C
Start-up	≥ -40 °C	Humidity	5...95 % rel. humidity, no condensation

Rated data UL

Certificate No. (cURus) E255651

Input

Connection system	SNAP IN	
AC input voltage range	85...264 V AC (derating at 100 V AC)	
Recommended back-up fuse	5 A / DI, safety fuse 6 A, Char. B, circuit breaker 4...6 A, Char. C circuit breaker	
Frequency range AC	45...65 Hz	
Rated input voltage	100...240 V AC / 120...340 V DC	
Surge protection	Varistor	
Input fuse	internal	
Wire connection method	SNAP IN	
DC input voltage range	110...370 V DC (derating at 120 V DC)	
Current consumption in relation to the input voltage	Voltage type	AC
	Input voltage	100 V
	Input current	2.58 A
	Voltage type	AC
	Input voltage	240 V
	Input current	1.07 A
	Voltage type	DC
	Input voltage	120 V
	Input current	2.2 A
	Voltage type	DC
	Input voltage	370 V
	Input current	0.74 A
Line regulation (typ.)	1 %	
Input electric strength, max.	300 V AC 15 s	
Nominal power consumption	256.7 VA	
Inrush current (typ.)	10 A	

PRO ECO 240W 24V 10A II SI

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Load regulation (typ.) 2 %

Start-up time, max. 1 s

Output

Output power 240 W

Max. residual ripple <50 mVPP / bandwidth 20 MHz

Connection system SNAP IN

Rated output voltage 24 V DC

Parallel connection option yes, max. 3

Overload protection Yes

Output voltage, max. 28 V

Output voltage, min. 22 V

Wire connection method SNAP IN

Output voltage, note (adjustable via potentiometer)

Nominal output current for Unom 10 A @ 55 °C

Line regulation (typ.) 1 %

Capacitive load unrestricted

Mains failure bridge-over time Mains failure bridge-over time, min. 31 ms

Input voltage type AC

Input voltage 230 V

Output current 10 A

Output voltage 24 V

Mains failure bridge-over time, min. 32 ms

Input voltage type AC

Input voltage 120 V

Output current 10 A

Output voltage 24 V

Protection against inverse voltage Yes

Continuous output current @ UNominal 6.25 A @ 70 °C

Load regulation (typ.) 2 %

Ramp-up time ≤ 100 ms

General data

AC failure bridging time @ Inom > 30 ms at 230 V AC / > 30 ms at 120 V AC

Degree of efficiency Typ.: 92,7% @ 120 V AC, Typ.: 94,5% @ 230 V AC

Humidity 5...95 % rel. humidity, no condensation

Protection degree IP20

Surge voltage category II

Mounting position, installation notice on terminal rail TS 35

Housing version Metal, corrosion resistant

Protection against reverse voltages from the load 30...35 V DC

Power factor Power factor typical 0.95

Input voltage 120 V

Ambient temperature 25 °C

Output power 240 W

Power factor typical 0.95

Input voltage 230 V

Ambient temperature 25 °C

Output power 240 W

Earth leakage current, max. 3.5 mA

Power loss, idling 4 W

Short-circuit protection Yes

Power loss, nominal load 20 W

Protection against over-heating Yes

PRO ECO 240W 24V 10A II SI

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

EMC / shock / vibration

Shock resistance IEC 60068-2-27	30 g in all directions	Noise emission in accordance with EN55032	Class B
Interference immunity test acc. to	EN 61000-4-2 (ESD), DIN EN 61000-4-3, EN 61000-4-4 (burst), EN 61000-4-5 (surge), EN 61000-4-6 (conducted), EN61000-4-8 (Fields), EN 61000-4-11 (Dips), IEC 61000-6-1, IEC 61000-6-2, IEC 61000-6-3, IEC 61000-6-4	Vibration resistance IEC 60068-2-6	0.7 g

Insulation coordination

Surge voltage category	II	Pollution severity	2
Protection class	I, with PE connection	Insulation voltage, input/output	4 kV
Insulation voltage input / earth	3 kV	Insulation voltage output / earth	0.5 kV

Electrical safety (applied standards)

Electrical machine equipment	Acc. to EN60204	Safety extra-low voltage	SELV acc. to IEC 61010-1, PELV acc. to IEC 61010-2-201
Safety transformers for switch-mode power supplies	According to EN 61558-2-16		

Connection data (input)

Connection system	SNAP IN	Number of terminals	3 for L/N/PE
Conductor cross-section, AWG/kcmil , max.	12 AWG	Conductor cross-section, AWG/kcmil , min.	20 AWG
Wire connection cross section, flexible (input), max.	4 mm ²	Conductor cross-section, flexible , min.	0.5 mm ²
Conductor cross-section, rigid , max.	4 mm ²	Conductor cross-section, rigid , min.	0.5 mm ²
Stripping length (input)	9 mm		

Connection data (output)

Connection system	SNAP IN	Number of terminals	4 (++ / -)
Conductor cross-section, AWG/kcmil , max.	12 AWG	Conductor cross-section, AWG/kcmil , min.	20 AWG
Conductor cross-section, flexible , max.	4 mm ²	Conductor cross-section, flexible , min.	0.5 mm ²
Conductor cross-section, rigid , max.	4 mm ²	Conductor cross-section, rigid , min.	0.5 mm ²
Stripping length (output)	9 mm		

Connection data (signal)

Wire connection cross-section, flexible (signal), max.	1.5 mm ²	Wire connection method	PUSH IN
Stripping length (Signal)	8 mm	Wire cross-section, AWG/kcmil , max.	14
Wire cross-section, solid , min.	0.2 mm ²	Wire cross-section, solid , max.	1.5 mm ²
Wire connection cross-section, flexible (signal), min.	0.2 mm ²	Number of terminals	2
Wire cross-section, AWG/kcmil , min.	28 mm ²		

PRO ECO 240W 24V 10A II SI

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Signalling

Floating contact	Yes	LED green	Operating voltage OK
Contact load (NO contact)	max. 30 V DC / 1 A		


Guarantee

Time interval	2 years
---------------	---------

Classifications




ETIM 6.0	EC002540	ETIM 7.0	EC002540
ETIM 8.0	EC002540	ETIM 9.0	EC002540
ETIM 10.0	EC002540	ECLASS 9.0	27-04-07-01
ECLASS 9.1	27-04-07-01	ECLASS 10.0	27-04-07-01
ECLASS 11.0	27-04-07-01	ECLASS 12.0	27-04-07-01
ECLASS 13.0	27-04-07-01	ECLASS 14.0	27-04-07-01
ECLASS 15.0	27-04-07-01		

Drawings



Status indicator and status relay

Operational status	Status LED	Relay contact (NO)
Fault-free operation: $U_{out} > 90\%$ of the set voltage	green	closed
Fault: $U_{out} \leq 85\%$ of the set voltage	red	opened
Overload pre-warning: $I_{out} > 90\% I_N$ (tolerance: $\pm 5\%$) and $U_{out} > 90\%$ of the set voltage	yellow	closed





PRO ECO 240W 24V 10A II SI

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Slotted screwdriver




VDE insulated screwdriver sets, for working on live parts up to 1000 V AC and 1500 V DC, DIN EN 60900. IEC 900. Each piece is "GS" safety tested. Blade made from fully hardened, high-alloy chromium-vanadium-molybdenum steel, gun-metal finish.

General ordering data

Type	SDIS SLIM 0.6X3.5X100	Version
Order No.	2749610000	Mounting tool, Blade width (B): 3.5 mm, Blade length: 100 mm, Blade
GTIN (EAN)	4050118896350	thickness (A): 0.6 mm
Qty.	1 ST	

End bracket



Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

General ordering data

Type	WEW 35/1 V0 GF SW	Version
Order No.	1478990000	End bracket, black, TS 35, V-0, Wemid, Width: 12 mm, 130 °C
GTIN (EAN)	4050118286892	
Qty.	50 ST	
Type	WEW 35/2 V0 GF SW	Version
Order No.	1479000000	End bracket, black, TS 35, V-0, Wemid, Width: 8 mm, 130 °C
GTIN (EAN)	4050118286779	
Qty.	50 ST	

Installation



Mounting accessory for Weidmüller Power Supplies.

PRO ECO 240W 24V 10A II SI

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

General ordering data

Type	MTA 30 BK	Version	
Order No.	1168970000	Electronics housings, Mounting flange, Accessories	
GTIN (EAN)	4032248960965		
Qty.	45 ST		