

Delock ZigBee 868 MHz Antenna SMA 2 dBi omnidirectional fixed

Description

This Delock 868 MHz antenna allows the use of SRD-Band Europa outdoors and indoors.



Item no. 88689

EAN: 4043619886890

Country of origin: Taiwan,
Republic of China

Package: Zip poly bag

Technical details

- Connector: SMA plug
- Frequency range: 868 MHz
- Antenna gain: 2 dBi
- Impedance: 50 Ohm
- Polarisation: linear, vertical
- VSWR: 2.0
- Return loss: -24.213 dB
- Operation temperature: -10 °C ~ 75 °C
- Antenna tube: TPU
- Tube colour: black
- Dimension (LxWxH): ca. 129.7 x 10.0 x 10.0 mm


System requirements

- Gerät mit freiem SMA Anschluss

Package content

- Antenna

Images



General

Suitable for indoor:	yes
Suitable for outdoor:	yes

Interface

Connector:	1 x SMA plug
------------	--------------

Technical characteristics

Frequency range:	868 MHz
Antenna gain:	2 dBi
Impedance:	50 Ω
Operating temperature:	-10 °C ~ 75 °C
Polarisation:	vertical linear
VSWR:	2.0

Physical characteristics

Antenna type:	omnidirectional
Housing colour:	black
Housing material:	TPU
Length:	129.7 mm
Width:	10.0 mm
Height:	10.0 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

