

Adapter USB Type-C™ to 1 x Serial RS-232 D-Sub 9 pin male with screws 0.25 m

Description

This USB Type-C™ to serial adapter by Delock provides a compatible RS-232 DB9 interface for printers, measuring instruments, controllers, IoT devices etc.



Item no. 64125

EAN: 4043619641253

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x USB Type-C™ male
 - 1 x serial DB9 male with screws
- Chipset: FTDI FT232RL
- Data transfer rate up to 230.4 Kbps
- Signals: TxD, RxD, RTS, CTS, DTR, DSR, DCD, RI, GND
- Cable length incl. connectors: ca. 0.25 m
- Colour: black

System requirements

- Linux Kernel 2.6 or above
- Mac OS 10.13 or above
- Windows 8.1/8.1-64/10/10-64/11
- PC or laptop with a free USB Type-C™ or Thunderbolt™ 3 port

Package content

- USB Type-C™ to 1 x serial adapter
- Driver CD
- User manual

Images



General

Function:	Plug & Play
Specification:	RS-232 (EIA / TIA) Thunderbolt™ 3 USB Type-C™
Supported operating system:	Linux Kernel 2.6 or above Mac OS 10.13 or above Windows 10 32-Bit Windows 10 64-Bit Windows 8.1 32-Bit Windows 8.1 64-Bit Windows 11

Interface

Output:	1 x Serial RS-232 DB9 male
Input:	1 x USB Type-C™ male

Technical characteristics

Chipset:	FTDI FT232RL
Data transfer rate:	460.8 Kbps
FIFO:	1 x 256 byte receiver 1 x 128 byte transmit
Data transmission:	asynchronous full duplex
UART:	USB to serial UART

Physical characteristics

Cable length incl. connectors:	25 cm
Pin finishing:	gold-plated
Cable gauge:	28 AWG data line 24 AWG power line
Screw type:	#4-40 UNC

Shielding:	double
Colour:	black

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de