

Antenna Cable SMA plug to SMA plug LMR195 low loss 10 m

Description

The antenna cable by Delock is suitable for connecting components of radio frequency technology.



Item no. 88893

EAN: 4043619888931

Country of origin: Taiwan,
Republic of China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x SMA plug >
 - 1 x SMA plug
- Impedance: 50 Ohm
- Cable type: LMR195
- Cable attenuation:
 - 0.59 dB per meter @ 2.4 GHz
 - 0.93 dB per meter @ 5.7 GHz
- Cable diameter: ca. 4.95 mm
- Cable colour: black
- Smallest bending radius: 12.7 mm
- Length incl. connectors (L): ca. 10 m

System requirements

- Device with two free SMA connectors

Package content

- Antenna cable

Images



General

Style:	both sides identical
--------	----------------------

Interface

Connector 1:	1 x SMA plug
Connector 2:	1 x SMA plug

Technical characteristics

Impedance:	50 Ω
------------	-------------

Physical characteristics

Cable type:	LMR195
Cable attenuation:	0.59 dB @ 2.4 GHz per meter 0.93 dB @ 5.7 GHz per meter
Cable colour:	black
Cable length incl. connectors:	10 m
Cable diameter:	4.95 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

