

Audio Converter Analogue > Digital HD

Description

The audio converter by Delock converts an analogue stereo signal into a digital signal. Two cinch cables can be connected to the device to input the analog source signal, e. g. from an MP3 player. At the output, the signal can be transmitted either via optical TOSLINK connection or via S/PDIF coaxial connection.



Item no. 63468

EAN: 4043619634682

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - Input:
 - 2 x RCA female
 - 1 x USB Type Micro-B female (5 V power supply)
 - Output:
 - 1 x TOSLINK female S/PDIF
 - 1 x Coaxial female S/PDIF
- Chipset: WM8805
- Sample rate: 16 Bit / 96 kHz
- Plastic housing
- Colour: black
- Dimensions (LxWxH): ca. 63 x 44 x 23 mm


System requirements

- Analogue audio signal
- Power source with a free USB Type-A female port

Package content

- Converter analogue > digital
- USB Type-A to Type Micro-B cable, length ca. 30 cm
- User manual

Images



Interface

Output:	1 x Coaxial female S/PDIF 1 x TOSLINK female S/PDIF
Input:	2 x RCA female (red, white) 1 x USB Type Micro-B female

Physical characteristics

Housing colour:	black
Housing material:	Plastic
Length:	63 mm
Width:	44 mm
Height:	23 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

