

TECHNICAL DATA

Producer	Qoltec
Scanner type	Wired
Scan Type	Laser
Input voltage	DC 5V 5%
Scanning speed	200 times/sec
Barcode Types	1D 2D
Decoding capability	1D : UPC-A , JAN/EAN-8, JAN/EAN-13 , Code 128, Code 39, Codabar, Code 93, Interleaved 2 of 5 , UPC-E UCC/EAN 128, GS1-128, ISBN-13, Industrial Standard 2 of 5 , Code 11, MSI Plessey, Code32, GS1 Composite, GS1 Databar, Composite, Matrix 2 of 5 2D : PDF417, Micro PDF 417, Micro QR Code, QR Code, Aztec code, Data Matrix, Maxicode
Scanning depth	QR Code 10.83mil 2cm - 9cm QR Code 20.83mil 2cm - 21cm Code 39 5.83mil 1cm - 12cm Code 39 10.83mil 1cm - 21cm EAN13 9.17 1cm - 15cm EAN13 10.83 2cm - 21cm
Scan mode	Manual, Continuous scanning
Scanning Angel	Rotation 360 , vertical 65 , yaw 65
Operating current	0.12A Standby) 0.18A Operating) 0.26A Max
Processor	32-bit ARM MCU + DSP
Print contrast	25%
Interface	USB
Shock resistance	1.2m
Resolution	Code39 4mil
Scanning distance	0mm - 400mm
Supported operating systems	Linux, Android, Windows XP, 7, 8, 10, MAC
Signalization	Sound
Cable length	~1.60m
Language	English, French, Dutch, German, Spanish (international), Italy (Italian 142), Turkish, Hungary,Russian, Japan, Swedish
Usage	Logistics Warehouses Commerce Libraries Airports Monitoring of medicines and medical supplies
Additional information	Error rate: 1/5000000
Other parameters	
Material	ABS + PC + TPU + PMMA
Colour	Black
IP Rating	IP52
Working temperature	0°C ~ +50°C
Working humidity	20-85% without condensation
Storage humidity	20-85% without condensation
Dimensions (D/L x W x H)	106 x 105 x 155 mm
EAN code	5901878508795