Antenna Cable SMA jack bulkhead to I-PEX Inc., MHF® 4L plug 1.37 20 cm thread length 10 mm

Description

The antenna cable by Delock is suitable for connecting components of radio frequency technology.

Item no. 90402

EAN: 4043619904020

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
  1 x SMA jack bulkhead >
  1 x I-PEX Inc., MHF® 4L plug
- Thread length: 10 mm
- Impedance: 50 Ohm
- Cable type: coaxial
- Cable type: 1.37
- Cable attenuation: 2.5 dB @ 2.4 GHz per meter
- Cable diameter: ca. 1.37 mm
- Smallest bending radius: 9.0 mm
- Cable colour: grey
- Cable length incl. connectors: ca. 20 cm

System requirements

- Device with one free SMA or I-PEX Inc., MHF® 4 port

Package content

All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**

- Antenna cable
- Nut and Locking Ring

Images

All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**

Interface

Connector 1:	1 x SMA jack bulkhead
Connector 2:	1 x I-PEX Inc., MHF® 4L plug

Technical characteristics

Impedance:	50 Ω

Physical characteristics

Thread length:	10 mm
Cable category:	coaxial
Cable type:	1.37
Cable attenuation:	2.5 dB @ 2.4 GHz per meter
Cable colour:	grey
Cable length incl. connectors:	20 cm
Smallest bending radius:	9 mm
Cable diameter:	1.37 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**