# Combo Converter for M.2 NVMe PCIe or SATA SSD with USB Type-C™ 10 Gbps

## Description




This converter by Delock enables the installation of an **M.2 PCIe NVMe SSD or SATA M.2 SSD**, it can be connected via USB to the PC or laptop.

**Combo converter**
The big advantage of this Delock M.2 converter is that both SATA and PCIe (NVMe) M.2 SSDs can be inserted into the converter. The **memory is automatically recognized by the chipset** and can then be used.

**Ideal test equipment**
The M.2 SSD is simply plugged into the slot and connected to the device via **USB-C™ plug**. Therefore, the converter is most suitable as test equipment.

**Item no. 64198**

EAN: 4043619641987

Country of origin: China

Package: Retail Box

## Technical details

- Connectors:
  1 x USB 10 Gbps USB Type-C™ male
  1 x M.2 key M slot
- Chipset: Realtek RTL9210B
- Supports M.2 modules with key M or key B+M based on SATA or PCIe (NVMe)
- Supports NVM Express (NVMe)
- Data transfer rate up to 10 Gbps
- LED indicator for power and access
- Bootable
- Plug & Play
- Cable length without connectors: ca. 10 cm

## System requirements

- Android 11.0 or above
- Chrome OS
- Linux Kernel 5.13 or above
- Mac OS 12.3.1 or above


All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**

- Windows 8.1/8.1-64/10/10-64/11
- iPad Air (4th Generation) or above
- iPad Pro (3rd Generation) or above
- PC or laptop with a free USB Type-C™ or Thunderbolt™ 3 port

## Package content

- M.2 converter
- User manual

## Images




All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**

## General

| | |
|---|---|
| Function: | Plug & Play<br>bootable |
| Supported operating system: | Chrome OS<br>Windows 10 32-Bit<br>Windows 10 64-Bit<br>Windows 8.1 32-Bit<br>Windows 8.1 64-Bit<br>iPad Pro (3rd Generation) or above<br>iPad Air (4th Generation) or above<br>Windows 11<br>Linux Kernel 5.13 or above<br>Mac OS 12.3.1 or above<br>Android 11.0 or above |
| LED indicator: | power and activity |

## Interface

| | |
|---|---|
| Connector 1: | 1 x USB 10 Gbps USB Type-C™ male |
| Connector 2: | 1 x 67 pin M.2 key M slot |

## Technical characteristics

| | |
|---|---|
| Chipset: | Realtek RTL9210B |
| Data transfer rate: | 10 Gbps |

## Physical characteristics

| | |
|---|---|
| Cable length: | 10 cm |

All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**

| | |
|---|---|
| Colour: | black |

All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**

## Manufacturer information

| | |
|---|---|
| Street | Beeskowdamm 13/15 |
| Postal code | 14167 |
| City | Berlin |
| Country | Deutschland |
| E-Mail | info@delock.de |
| Website | www.delock.de |

All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**