Belden



Product: 9430

Electronic, 7 C #22 Str TC, PVC Ins, PVC Jkt, CMG

Request Sample

Product Description

Electronic, 7 Conductor 22AWG (7x30) Tinned Copper, PVC Insulation, PVC Outer Jacket, CMG

Technical Specifications

Product Overview

Suitable Applications:	low voltage analog signals (4-20ma, 0-10v, ...); low voltage control (24v, …); line level audio; voice communications; panel wiring

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	7	22 AWG	7x30	TC - Tinned Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	PVC - Polyvinyl Chloride	0.011 in (0.28 mm)	0.050 in (1.3 mm)	Black, White, Red, Green, Brown, Blue, Orange

Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.032 in (0.81 mm)	0.214 in (5.44 mm)

Overall Cable Diameter (Nominal):	0.214 in (5.44 mm)

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Inductance	Max. Current
Conductor(s)	15.6 Ohm/1000ft	34 pF/ft (110 pF/m)	0.17 µH/ft (0.56 µH/m)	2.1 Amps per Conductor at 25ºC

Voltage

UL Voltage Rating
300 V (CMG), 150 V (UL AWM 2576)

Mechanical Characteristics

Temperature

UL Temperature	Operating
80°C	-20°C to +80°C

Bend Radius

Stationary Min.	Installation Min.
2.1 in (53 mm)	2.1 in (53 mm)

Max. Pull Tension:	64 lbs (29 kg)
Bulk Cable Weight:	30 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor (Not Riser or Plenum), Indoor

Flammability / Reaction to Fire:	UL 1685 FT4 Loading, FT4, IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 800, CMG
AWM Compliance:	AWM 2576
CEC / C(UL) Compliance:	CMG
European Directive Compliance:	EU CE Mark, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark

History

Update and Revision:	Revision Number: 0.515 Revision Date: 09-07-2025

Part Numbers

Variants

Item #	Color	UPC	Footnote
9430 0601000	Chrome	612825245025	C
9430 060500	Chrome	612825245032	C
9430 0605000	Chrome	612825399711	
9430 060U1000	Chrome	612825245001	
9430 060U500	Chrome	612825245018	

Footnote:	C - CRATE REEL PUT-UP.

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.