



Product: [19510](#) 

Portable Cordage, 3 C #16 Str BC, PVC Ins, PVC Jkt, UL Type SJTOW-A

 [Request Sample](#)

Product Description

Portable Cordage, 3 Conductor 16AWG (65x34) Bare Copper, PVC Insulation, PVC Outer Jacket, UL Type SJTOW-A

Technical Specifications

Product Overview

Suitable Applications:	Portable cordage and cordage
------------------------	------------------------------

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	3	16	65x34	BC - Bare Copper

Insulation

Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
PVC - Polyvinyl Chloride	0.033 in (0.84 mm)	0.124 in (3.15 mm)	Green/Yellow, Brown, Blue

Outer Jacket

Separator	Material	Nom. Thickness	Nom. Diameter
Paper Tape	PVC - Polyvinyl Chloride	0.038 in (0.97 mm)	0.34 in (8.6 mm)

Electrical Characteristics

Electricals

Nom. Conductor DCR	Max. Current
4.4 Ohm/1000ft	13 Amps per Conductor at 25°C (10 Amps over 50 ft)
	10 Amps per Conductor at 25°C (over 50 ft)

Voltage

UL Voltage Rating
300 V

Mechanical Characteristics

Temperature

UL Temperature	Operating
60°C	-35°C To +105 °C

Bend Radius

Stationary Min.	Installation Min.
3.4 in (86 mm)	3.4 in (86 mm)

Max. Pull Tension:	105.3 lbs (47.76 kg)
Bulk Cable Weight:	64 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Outdoor, Oil Resistance
----------------------------	-------------------------

Flammability / Reaction to Fire:	VW-1
NEC / UL Compliance:	Article 400, SJTOW
AWM Compliance:	SJTOW
European Directive Compliance:	EU CE Mark, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

Product Notes

Notes:	Approved as water resistant, oil resistant and outdoor use.
--------	---

History

Update and Revision:	Revision Number: 0.501 Revision Date: 09-07-2025
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
19510 B59250	Black, Matte	Reel	250 ft	612825127185	C
Footnote:		C - CRATE REEL PUT-UP.			

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.