


QuickSpot®

Luminescent Cable Ties

Natural

- GLOW-IN-THE-DARK
- UL 94 V-2
- HALOGEN-FREE
- ROHS COMPLIANT



Technical specification

Material	Polyamide 6.6 + photoluminescent additive
Colour	Natural
Luminescence	Clear glow ≥30 min after light exposure; residual afterglow for several hours
Flammability	UL 94 V-2
Halogen-free	Yes
Moisture absorption	2.7% at 23 °C and 50% R.H.
Working temperature	-40 °C to +85 °C
Installation temperature	-10 °C to +60 °C
Resistant to	Aromatic solvents, oils, greases and derivatives
Limited resistance	Acids
Not resistant to	Phenols and chlorinated solvents

Range & item codes

ITEM CODE	SIZE	W (MM)	L (MM)	MAX Ø (MM)	N	KGF	PCS/PACK	PCS/CARTON
01 STANDARD 2.5 / 3.6 MM Low-light identification, temporary marking and maintenance work where short-term visibility after light exposure is useful.								
TT3X100L	2.5X100 mm	2.5	100	Ø22	80	8	100	28,000
TT3X150L	2.5X150 mm	2.5	150	Ø35	80	8	100	21,000
TT3X200L	2.5X200 mm	2.5	200	Ø50	80	8	100	16,000
TT3X250L	2.5X250 mm	2.5	250	Ø65	80	8	100	14,000
TT4X150L	3.6X150 mm	3.6	150	Ø35	178	18	100	12,000
TT4X200L	3.6X200 mm	3.6	200	Ø50	178	18	100	10,000
TT4X250L	3.6X250 mm	3.6	250	Ø65	178	18	100	8,000
TT4X300L	3.6X300 mm	3.6	300	Ø80	178	18	100	7,000
TT4X370L	3.6X370 mm	3.6	370	Ø100	178	18	100	6,000
02 INSTALLATION 4.6 MM Service routes, technical rooms and maintenance areas where medium-width luminescent ties support installation work.								
TT5X200L	4.6X200 mm	4.6	200	Ø50	216	22	100	7,000
TT5X250L	4.6X250 mm	4.6	250	Ø65	216	22	100	6,500
TT5X300L	4.6X300 mm	4.6	300	Ø80	216	22	100	5,000
TT5X350L	4.6X350 mm	4.6	350	Ø90	216	22	100	4,500
TT5X400L	4.6X400 mm	4.6	400	Ø105	216	22	100	5,000
TT5X450L	4.6X450 mm	4.6	450	Ø120	216	22	100	5,000
TT5X500L	4.6X500 mm	4.6	500	Ø150	216	22	100	4,500
03 REINFORCED 7.6 MM Larger bundles where short-term visibility helps identify cables, fixing points and cut-off tie tails.								
TT8X300L	7.6X300 mm	7.6	300	Ø80	540	55	100	3,000
TT8X400L	7.6X400 mm	7.6	400	Ø105	540	55	100	3,000
TT8X500L	7.6X500 mm	7.6	500	Ø150	540	55	100	2,500

N / kgf = minimum loop tensile strength.

↳ Helps spot cut-off ends in low-light areas.