Antenna Cable FAKRA F jack to open wires RG-316 20 cm 2 prepunched holes

Description

The antenna cable by Delock is suitable for connecting components of radio frequency technology.



Item no. 90733

EAN: 4043619907335

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
  1 x FAKRA F jack
  1 x open wire end
- FAKRA F: RAL 8011 Nut brown
- Impedance: 50 Ohm
- Cable type: RG-316
- Cable type: coaxial
- Cable diameter: ca. 2.6 mm
- Cable attenuation: 2 dB @ 2.4 GHz per meter
- Smallest bending radius: 10.5 mm
- Mounting plate: steel
- 2 prepunched holes for mounting
- Thread type: M3
- Cable length without connectors: ca. 20 cm
- Dimensions (LxWxH): ca. 24 x 12 x 9 mm

Package content

- Antenna cable

All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**

Images



All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**

Interface

Connector 1:	1 x FAKRA F jack
Connector 2:	1 x open end tinned

Physical characteristics

Cable type:	RG-316
Cable length:	20 cm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**