

LTE Antenna SMA plug 3 - 5 dBi 12.5 cm fixed omnidirectional with magnetic base and connection cable RG-174 A/U 3 m outdoor black

Description

This antenna by Delock allows the usage of different LTE bands outdoors.



Item no. 12588

EAN: 4043619125883

Country of origin: China

Package: Box

Technical details

- Connector: 1 x SMA plug
- Frequency range:
698 MHz - 960 MHz
1710 MHz - 2170 MHz
2500 MHz - 2700 MHz
- ZigBee, LoRa, DECT, Z-Wave, NB-IoT, Bluetooth, GSM, UMTS, LTE, ISM, WLAN
- Antenna gain: 3 - 5 dBi
- Impedance: 50 Ohm
- VSWR: 1.5
- Polarisation: linear, vertical
- Operating temperature: -20 °C ~ 70 °C
- Housing material: ABS
- Colour: black
- Protection class: IPX5
- Cable: coaxial
- Cable type: RG-174 A/U
- Cable colour: black
- Cable attenuation: 1.5 dB @ 1.5 GHz per meter
- Cable diameter: ca. 2.7 mm
- Cable length incl. connector: ca. 3 m
- Dimensions (LxD): ca. 1250 x 29.0 mm


System requirements

- Device with a free SMA connector

Package content

- Antenna

Images



General

Mounting type:	magnetic
Protection class:	IPX5
Suitable for outdoor:	yes

Interface

Connector:	1 x SMA plug
------------	--------------

Technical characteristics

Frequency range:	2500 - 2700 MHz 1710 - 2170 MHz
Antenna gain:	3 - 5 dBi
Impedance:	50 Ω
Operating temperature:	-20 °C ~ 70 °C
Polarisation:	linear vertical
VSWR:	1.5

Physical characteristics

Housing material:	ABS
Cable category:	coaxial
Cable type:	RG-174 A/U
Cable attenuation:	1.5 dB @ 1.5 GHz per meter
Cable colour:	black
Cable length incl. connectors:	3.0 m
Dimensions (LxD):	125.0 x 29.0 mm
Cable diameter:	2.7 mm

Manufacturer information

Street Beeskowdamm 13/15

Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

