

MCHQ80V24-GE



- Features:**
- European AC input(200-277VAC)
 - Built-in active PFC function
 - IP67, Metal Case
 - Suitable for dry, humid and rainy environment
 - Protections: Short circuit / Over voltage / Over temperature
 - Adopt metal shell and internal glue filling, can be used in dangerous situations
 - Built in lightning protection device can meet the requirements of DM 4KV / CM 6kV
 - Compliance to worldwide safety regulations for lighting
 - 5 years warranty

CE IP67 SELV UK CA

ELECTRICAL SPECIFICATION

Product Type	LED Driver,Power supply
Output Voltage	24V DC
Rated Current	3.33 A
Power (W)	80 W
Dimming	No
Voltage Ripple & Noise (max.)	±2% @ Full load
Line Regulation	±1%
Load Regulation	±2%
Setup, Rise Time	400ms, 100ms / 230VAC
AC input voltage range	European
PFC	Yes
Protection class	I
Efficiency (typ.)	89%
AC Current (typ.)	0.41A max, 230VAC Full Load
No Load Power Consumption (typ. / max.)	0.3W / 0.5W
Inrush Current (typ.)	Cold Start 60A @ 230VAC
IP protection level	IP67
Leakage Current (max.)	max 0.7 mA 230 V AC, full load

Over Current / Overload protection	Type: auto-recovery.
Over Current / Overload protection (range)	140% rated output load
Short Circuit protection	Type: hiccup mode, auto-recovery.
Over Voltage protection (range)	150% rated output voltage
Over Voltage protection	Type: shut down output voltage. Re-power on to recovery.
Over Temperature protection	Type: shut down output voltage. Re-power on to recovery.
Working Temperature range	-40~+55°C
Working Humidity range	10 ÷ 90% RH non-condensing
Storage Temperature and Humidity	-40°C ÷ 80°C, 10 ÷ 95% RH non-condensing
Safety Standards	EN61347-1,EN 61347-2-13
Withstand Voltage	I/P-O/P: 3200VAC/5mA Max 60s, O/P-FG 1000V AC/5mA max 60s, I/P-FG 1600V AC/5mA max 60s
Isolation Resistance	≥10MΩ
EMC Emission	EN55015,EN62493:2015
EMC Emission	EN61000-3-2 Class C
Harmonic Current	EN61000-3-2 Class C
Dimensions (L x W x H)	157x52.9x36x5 mm
Weight (kg)	0.5
Packing	15 pcs/box
Warranty	7 years
Mounting	surface
Programmable	No

MECHANICAL SPECIFICATION

