


## ROCKER SWITCH MODEL: R SERIES




RATING:16(4)A 125/250V~ (cURus5)

16(4)A 250V~ T125/55 (ENEC15/CQC)

DIELECTRIC WITHSTAND VOLTAGE: 1500VAC 1 MIN

INSULATION RESISTANCE:500VDC 100MΩ (MIN)

CONTACT RESISTANCE:20mΩ INITIAL(MAX.)



NOTE: TOLERANCES UNLESS OTHERWISE SPECIFIED: ± .012/ 0.3 (in/mm)

| REVISION   | DESCRIPTION | REVISED BY | TOLERANCES |     |             | ANGLE $\frac{1}{2}^\circ$ |       | UNIT       | mm      | PART NAME           | DWG NO  |
|------------|-------------|------------|------------|-----|-------------|---------------------------|-------|------------|---------|---------------------|---------|
|            |             |            | DRAWN BY   | 达志各 | DESIGNED BY | 蔡剑                        | SCALE | 5/4        |         | R SPEC DRAWING      | S10112A |
|            |             |            | CHECKED BY |     | APPROVED BY |                           | DATE  | 2024.11.21 | PART NO | R-210T5W-N**A-11BNC |         |
|            |             |            |            |     |             |                           |       |            |         |                     |         |
| 2024.11.21 | 首次出圖        | 奚康平        |            |     |             |                           |       |            |         |                     |         |