

客户 (Customer): 2025-06-20AD

发行编号: 2022040201

发行日期: 2022.04.02

发行区分: ☒ 新规 ☐ 改定


规格承认书

SPECIFICATION FOR APPROVAL

轻触开关 Tact Switch

产品名称 Description: SMT Flat type/ 2.8X4.2 series H:1.9mm/ Non earth terminal/
200gf/ PPA stem/ Black color

产品型号 Part No.: TVAF47-019FB-S-R



接受印

ACKNOWLEDGEMENT

兹证明此份材料已经收到。

WE ACKNOWLEDGE RECEIVING THIS DOCUMENT.

MONTH / DAY / YEAR

DATE: / /

浙江键富电子有限公司
ZHEJIANG JIANFU ELECTRONICS CO., LTD

地址: 浙江乐清天成工业区宁康东路 2892 号

TEL: 0577-61302223

FAX: 0577-61301196

Email: sales03@jian-fu.com

发行部门: 技术部

拟制	核对	审核	批准
研 发 部 22.04.02 张 鹏	研 发 部 22.04.02 万 旭 燃	品 管 部 22.04.02 梁 丽 美	总 经 办 22.04.02 赵 高 杰

JIANFU

规格承认书				规格书编号 2022040201
品 名	2.8X4.2X1.9 PPA stem	型 号	TVAF47-019FB-S-R	1/10
1. General Specification 基本说明				
1.1 Scope 范围 This specification covers the requirements for single key switches which have no key top(TACT SWITCHES:MECHANICAL CONTACT).此规范含盖单推柄和无推柄的轻触开关要求				
1.2 Operating Temperature Range 使用温度范围 -40 ~85℃(normal humidity, normal press.) 正常湿度，标准压力				
1.3 Storage Temperature Range 保存温度范围 -40 ~85℃(normal humidity, normal press.)				
1.4 Test Conditions 测试条件 Tests and measurements shall be made in the following standard conditions unless otherwise specified: 测试和计量按下列标准条件除非特殊说明 Normal temperature (temperature 5 ~35℃) 标准温度 Normal humidity (relative humidity 25 ~85%) 正常湿气 Normal pressure (pressure 86 ~106 Kpa) 标准压力 In case any question arises from the judgment made, tests shall be conducted in the following conditions: Temperature (20±2℃) 温度 Relative humidity (60 ~70%) 相对湿度 Pressure (86 ~106Kpa) 压力				
2. Type Of Actuation 动作类型 <u>Tactile feedback</u> 轻触返回				
3. Contact Arrangement 1 poles 1 throws 接触形式 1 回路 1 接点 (Details of contact arrangement are given in the assembly drawings.) 细接点形式在装配图中				
4. Maximum Ratings DC 32 V 50 mA 最大额定值 DC 20 mV 1 mA 最小额定值				

规格书编号	2022040201
-------	------------


2/10

5.1 外形图:

ZHEJIANG JIANFU ELECTRONICS CO., LTD

规格承认书				规格书编号 2022040201
品 名	2.8X4.2X1.9 PPA stem	型 号	TVAF47-019FB-S-R	3/10


5.2 构造:



序号	零部件名称	数量	材料名称	表面处理	备注
1	COVER	1	SUS		
2	STEM	1	PPA		BLACK
3	TAPE	1	GATHERS THE IMIDE		YELLOW
4	CONTACT FORM	2	SUS	Silver coated	
5	HOUSING	1	PA		BLACK
6	TERMINAL	1	BRASS	Ag plating	

规格承认书				规格书编号 2022040201
品 名	2.8X4.2X1.9 PPA stem	型 号	TVAF47-019FB-S-R	4/10

6. General Specification 电气性能

Item 项目		Test Condition 测试条件	Requirements 要求
6.1	Contact Resistance 接触电阻	Applying static load twice the actuating force to the center of the stem, measurements shall be made with a 1 kHz small-current contact resistance meter. 用两倍的动作力作静负载施加于按钮的中心,并用 1 千赫小电流接触电阻仪测量	<u>100</u> mΩ 以下
6.2	Insulation Resistance 绝缘电阻	Measurements shall be made following application of DC <u>100</u> V potential between terminals and between individual terminals and frame for one minute.在端子与端子之间,端子与外壳之间施加 DC100V, 一分钟	<u>1</u> GΩ 以上
6.3	Dielectric Withstanding Voltage 电气耐压	AC <u>250</u> V(50Hz or60Hz) shall be applied between terminals and between individual terminals and frame for one minute. 在端子与端子之间,端子与外壳之间施加 AC250V(50HZ-60HZ)一分钟	There shall be no breakdown. 无击穿、闪烁现象
6.4	Bounce 抖动	Lightly striking the center of the stem at a rate encountered in normal use (3 to 4 operations per sec), Bounce shall be tested when “ON” and “OFF”. 在正常使用中(以每秒 3-4 回)轻轻地在手柄中心加力,在通与断瞬间测试抖动  t 为触点抖动时间	<u>5</u> mS 以下

规格承认书				规格书编号 2022040201
品 名	2.8X4.2X1.9 PPA stem	型 号	TVAF47-019FB-S-R	5/10
7.Mechanical specification 机械的性能				
Item 项目		Test Condition 测试条件	Requirements 要求	
7.1	Operating Force 动作力	Placing the switch such that the direction of switch operation is vertical and then gradually increase the load applied to the top center of the stem.the maximum load required for the switch to come to a stop shall be measured . 开关的动作方向为垂直放置开关向推柄中心逐渐地增加负荷到推柄停止时所测量的最大负荷。	200 ± 50 gf (2 ± 0.5 N)	
7.2	Travel 行程	Placing the switch such that the direction of switch operation is vertical and then applying a below static load to the top center of the stem.the travel distance for the switch to come to a stop shall be measured. 开关的动作方向为垂直放置开关并以双倍动作力的静负荷作用推柄中心，测量推柄中心从开始到停止的行程距离。	0.2 ± 0.1 mm	
7.3	Return Force 返回力	The sample switch is installed such that the direction of switch operation is vertical and, upon depression of the stem in its center the whole travel distance , the force of the stem to return to its free position shall be measured.开关的动作方向为垂直放置开关, 在已有行程的推柄中心向上减少压力，推柄回到自由位置时所测量到的力.	50 gf min	
7.4	Static Strength 静止强度	Placing the switch such that the direction of switch operation is vertical and then a below static load shall be applied in the dirction of stem operation. 开关的动作方向为垂直放置开关,开关操作方向施加以下静核重量 (1)Depression 按压力 : 1N (2) Direction: 时间 : 15 s (3)Number of times 回数 : 1 time	There shall be no sign of damage mechanically and electrically. 无机械的和电气的损伤迹象	

规格承认书				规格书编号 2022040201
品 名	2.8X4.2X1.9 PPA stem	型 号	TVAF47-019FB-S-R	6/10


8. Environmental specification 使用耐候性能

Item 项目		Test Condition 测试条件	Requirements 要求
8.1	Moisture Resistance 耐潮湿	Following the test set forth below the sample shall be left in normal temperature and humidity conditions for one hour before measurements are made: 样品按下列条件进行耐潮湿试验, 试验后在正常温度和湿度条件下放置 1 小时后测定 (1) Temperature: 60±2℃ 温度 (2) Relative humidity: 90 to 95% 相对湿度 (3) Time: 96 hours 时间 Water drops shall be removed. 擦除水珠	Contact resistance: 500 mΩ Max. 接触电阻 Insulation resistance : 10 MΩ Min. 绝缘电阻 Item 6.3、6.4 Item 7
8.2	Low Temperature Resistance 耐低温	Following the test set forth below the sample shall be left in normal temperature and humidity conditions for one hour before measurements are made: 样品按下列条件进行耐低温试验, 试验后在正常温度和湿度条件下放置 1 小时后测定 (1)Temperature: -40±2℃ 温 度 (2) Time: 96 hours 时 间 Water drops shall be removed. 擦除水珠	Item 6 Item 7
8.3	Heat Resistance 耐热	Following the test set forth below the sample shall be left in normal temperature and humidity conditions for one hour before measurements are made: 样品按下列条件进行耐热试验, 试验后在正常温度和湿度条件下放置 1 小时后测定 (1)Temperature: 85±2℃ 温 度 (2) Time: 96 hours 时 间	Item 6 Item 7
8.4	Change of Temperature 温度循环	Following ten cycles of high temperature test .The Sample shall be Placed in Normal temperature and humidity Conditions for one hour before measurements are made. During this test, water drops shall be removed. 样品按下列条件进行高低温循环试验,试验后在正常温度和湿度条件下放置 1 小时后测定 温度(℃) A: +60℃ B: -10℃ C: 2 小时 D: 1 小时 E: 2 小时 F: 1 小时 1 cycle 时间(hour) (1)Number of cycles 周 期: 5 cycles	Item 6 Item 7

规格承认书				规格书编号 2022040201
品 名	2.8X4.2X1.9 PPA stem	型 号	TVAF47-019FB-S-R	7/10

9. Environmental specification 使用耐久性能

Item 项目		Test Condition 测试条件	Requirements 要求
9.1	Operating Life 动作寿命	Measurements shall be made following the test set forth below:按下列条件进行寿命试验 (1)DC 5V 5mA resistive load. DC 5V 5mA 阻性负载 (2)Rate of operation:2 to 3 operations per second 动作频率:2-3 次/每秒 (3)Depression: <u>300</u> gf 按压力 (4)Cycles of operation: 20×10^4 cycles 动作次数: 20×10^4 次	Contact resistance: <u>1</u> Ω Max. 接触电阻 Insulation resistance : <u>10</u> M Ω Min.绝缘电阻 Bounce:<u>20</u>ms Max 抖动 Operating force: 动作力 $\pm 30\%$ of initial force. $\pm 30\%$初始动作力 Item 6.3
9.2	Vibration Resistance 耐振动	Measurements shall be made following the test set forth below: 按下列条件进行抗振动试验 (1)Range of oscillation: 10 to 55Hz 频率范围 (2)Amplitude,pk-to-pk:1.5mm 振幅:峰-峰 1.5mm (3)Cycle of sweep: 10-55-10Hz in one minute, approx.扫描周期: 10-55-10Hz 约一分钟内 (4)Mode of sweep: Logarithmically sweep or uniform sweep. 扫描方式: 对数扫描式恒定扫描 (5)Direction of oscillation: 振动方向 Three mutually perpendicular directions, including the direction of stem travel. 3 个相互垂直方向,包括推柄行程方向 (6)2 hours each ,for a total of 6 hours.每方向 2 小时.共 6 小时	Item 6 Item 7
9.3	Impact Shock Resistance 抗冲击	Measurements shall be made following the test set forth below: 按下列条件进行冲击试验 (1) Acceleration: 784m/s^2 加速度 (2)Cycles of test : 3 cycles each in 6directions, for a total of 18cycles 试验 次数: 每个方向 3 次, 6 个方向共 18 次	Item 6 Item 7



规格承认书				规格书编号 2022040201
品 名	2.8X4.2X1.9 PPA stem	型 号	TVAF47-019FB-S-R	8/10
10. Soldening conditions 焊接条件:				
Item 项目		Recommended conditions 推荐条件		
10.1	Hand Soldering 手工焊接	Please practice according to bellow conditions: (1)Soldering temperature : 350℃ Max (2)Continuous soldering time: 3 S Max (3)Capacity of soldering iron: 20 W Max 请按以下条件进行焊接: (1)焊锡温度: 350℃ Max (2)连续焊接时间: 3 S Max (3)电烙铁的功率: 20 W Max		
10.2	Automatic Flow Soldering 自动焊接	For the product of SMT ,type solder according to the following conditions 对于SMT产品, 请按以下条件进行焊接 surface of product temperature 部品表面温度 (℃) 230℃ 180℃ 150℃ 室温 120sec max. pre-heating(预热) 40s max. 3 ~ 4min. max. 260℃ max. 3sec max. peak temperature time 时间(秒) time inside soldering equipment 炉内通过时间 Caution: the condition mentioned above is a temperature on the PWB surface on which parts are mounted. There are cases where PWB temperature greatly differs from switch's surface temperature depending on PWB material, size, thickness, etc. The switch's surface temperature shall not allowed to exceed 260℃ 注意: 以上提及的条件是零部件上 PWB 表面的温度, 由于PWB 的材料、尺寸、厚度等不同, PWB 从开关表面获得的温度也会有很大产不同, 因此, 千万小心不要让开关表面温度超过 260℃ Twice soldering would be reflow the temperature goes down to a normal temperature 两次回流焊接温度降到正常温度		
10.3	Solderability 可焊性	Measurements shall be made following the test set forth below: 按下列条件进行试验 (1)Soldering Temperature:245±3℃ 焊接温度:245±3℃ (2)Flux:5-10 sec 助焊剂: 沾覆5±1 秒 (3)Duration of solder mmersion: 5±1sec 浸焊时间: 5±1sec	Soldering area is greater than 75% of the total area. 焊锡面积大于总面积的 75%	
11. Protection grade 保护等级:				
Item 项目		Test Condition 测试条件	Requirements 要求	
11.1	IP40 防护等级	The switch is located in the dust-proof experimental box and should not enter dust at a low pressure of 20mbar. 开关在防尘实验箱体内部, 在20毫巴的低压时不应进入灰尘	Completely prevent dust intrusion 完全防止灰尘侵入	

规格承认书				规格书编号 2022040201
品 名	2.8X4.2X1.9 PPA stem	型 号	TVAF47-019FB-S-R	9/10

12. Other Precautions 其他注意事项:

- (1) Following the soldering process, do not try to clean the switch with a solvent or the like.
进行焊接过程中，不可以用溶剂或类似品清洗开关
- (2) Safeguard the switch assembly against flux penetration from its topside.
防止助焊剂从开关的顶端渗入
- (3) Please have the products keep in close status and the storage time is 90 days guaranty after delivering the goods at most.
交货后保证开关处于封密状态并库存时间 90 天以下

13. Reel Packaging 盘装

13.1 Scope 范围

This specification covers the requirements of the reel packaging for SMT standard type of tact switches. 该规范包含 SMT 标准型贴片开关的绕带封装的要求



13.2 Packaging Materials 封装材料

Item	项 目	Description	说 明
Package	包 装	Cartons	卡通箱
Reel	转 轴	Delete Cartons	可降解箱
Carrier Tape	载 带	Polypropylene	聚丙烯


13.3 Packaging Quantity 封装数量

- 13.3.1 The number of the reels. 转 轴 数 量
Fifteen (20) reels at maximum. Which contain 80K pcs switches
Shall be packed in a package. 一箱装 20 盘,有 80K 只产品
- 13.3.2 The number of the switches. 产品数量
4K pcs switches shall be packed in a reel. 一个转轴包 4K 只产品
- 13.3.3 It should be noted that we regard two cartons 对出口包装需注意用两个箱子包装
mentioned above as on package for export.



* THE DIMENSION OF CARRIER TAPE, COVER TAPE AND REEL *




* END TAPE *



* THE SPECIFICATION FOR PACKAGING *



* THE SPECIFICATION FOR PACKAGING *



NOTE

1. 4K pcs SWITCHES PER 1 REEL
2. GENERAL TOLERANCE : 0.3mm

REFERENCE DRAWING

Designed by			浙江健富电子有限公司 ZHEJIANG JIANFU ELECTRONICS CO., LTD				
Checked by			mm	Scale	N/S	Date	2022.06.02
Approved by			Unit	Tool	Sheet	1/1	Rev.
Item	TACT SWITCH		A-Cad			1	
Model	2.8X4.2	Drawing name ASSEMBLY					