


TAH16B

1/2" Square Drive Sockets with Metric Bi-Hex Profile and 4 Point Solution

PRODUCT DETAILS

- Not suitable for machine operation
- Knurled
- Highly polished finish
- High-performance alloy steel
- Standards: ISO 2725/1174, DIN 3124/3120
- Suitable for working at height
- 4 side lock holes ensure positive retention and full functionality
- Colour plate with maximum weight to match with lanyard
- According to DROPS best practices



Follow the Fish!

PRODUCT ATTRIBUTES

Product	⌀	L	D1	D2	T	g
TAH16B-8	8 mm	38 mm	12.4 mm	22 mm	12.3 mm	42 g
TAH16B-10	10 mm	38 mm	15.4 mm	22 mm	13.4 mm	51 g
TAH16B-11	11 mm	38 mm	16.6 mm	22 mm	14.3 mm	40 g
TAH16B-12	12 mm	38 mm	18 mm	22 mm	14.6 mm	51 g
TAH16B-13	13 mm	38 mm	19 mm	22 mm	14 mm	56 g
TAH16B-14	14 mm	38 mm	20.4 mm	22 mm	14 mm	56 g
TAH16B-15	15 mm	38 mm	21 mm	21 mm	14 mm	50 g
TAH16B-16	16 mm	38 mm	23 mm	23 mm	14 mm	64 g
TAH16B-17	17 mm	38 mm	24.1 mm	23 mm	14 mm	72 g
TAH16B-18	18 mm	38 mm	25.4 mm	24 mm	18.3 mm	76 g
TAH16B-19	19 mm	38 mm	26.6 mm	24 mm	18.4 mm	70 g
TAH16B-21	21 mm	38 mm	28 mm	26 mm	19.4 mm	80 g
TAH16B-22	22 mm	41 mm	30 mm	26 mm	21.6 mm	90 g
TAH16B-24	24 mm	41 mm	32 mm	26 mm	22.2 mm	100 g
TAH16B-25	25 mm	41 mm	33 mm	28 mm	22.4 mm	110 g
TAH16B-27	27 mm	44 mm	36 mm	30 mm	24.5 mm	140 g
TAH16B-30	30 mm	44 mm	40 mm	29 mm	24 mm	180 g
TAH16B-32	32 mm	44 mm	42 mm	36 mm	24.6 mm	200 g