

Technical data // SH6 131 AK 2

Dual Push Button Switches

Dual Push button Switch



Highlights

Contacts with abrasion resistant hard gold plating

100 % electronic final inspection and testing

Mechanical Data

Width	6.0 mm
Perm. ambient temperature	-20 °C ... +80 °C
Mechanical lifetime	100.000 steps
Operating force	approx. 4.0 N
Weight	approx. 1.5 g
Digit height 10-digit	3.1 mm
Digit height 16-digit	4.3 mm
Click action	marked
Sinus-vibration testing	acc. EN 60068-2-6
Shock testing	acc. EN 60068-2-27

Electrical Data

Operating voltage	≤ 40.0 V
Contact load, dynamic (resistive)	≤ 100.0 mA
Contact load, static	≤ 1.0 A
Contact resistance for PCB AK (measured from supply line to output)	< 100.0 mOhm

Material

Housing	PPO
Contact surface	Au over Ni on Cu
Sliding contact	Au over Ni on CuSn6



PTR HARTMANN

A Phoenix Mecano Company


Technical data

// SH6 131 AK 2

Dual Push Button Switches


Dual Push button Switch

Technical Drawing



Configuration

Type



SH6



PTR HARTMANN

A Phoenix Mecano Company

Technical data

// **SH6 131 AK 2**

Dual Push Button Switches

Dual Push button Switch


Codes

Code 131

BCD					
	C	1	2	4	8
0	●				
1	●	●			
2	●		●		
3	●	●	●		
4	●			●	
5	●	●		●	
6	●		●	●	
7	●	●	●	●	
8	●				●
9	●	●			●

BCD, 10

PCB



Short

Colour

Housing black, drum black,
digits white