

Audio Converter Digital > Analogue

Description

The audio converter by Delock converts a digital audio signal into an analogue stereo signal. For example a DVD or Blu-ray player can be connected to the input of the device and the signal can be supplied via optical TOSLINK or via S/PDIF coaxial connection. At the output port, the audio signal is transmitted via the RCA connection.



Item no. 62444

EAN: 4043619624447

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
Input:
1 x TOSLINK female S/PDIF
1 x Coaxial female S/PDIF
1 x DC jack
Output:
2 x RCA female
- Supported sample rates: 32 / 44.1 / 48 / 96 kHz
- Robust metal housing
- Dimensions (LxWxH): ca. 63 x 41 x 21 mm

Power supply specification

- Power supply type: Euro wall power plug
- Model identifier: FJ-SW1160501000DE
- Input voltage: 100 - 240 V
- Input AC frequency: 50 / 60 Hz
- Input current: 0.3 A
- Output voltage / Output current / Output power: 5.0 V / 1.0 A / 5.0 W
- Average active efficiency: 75.7 %
- No-load power consumption: 0.07 W
- DC power connector: 5.5 x 2.1 mm
- Power supply cable length: ca. 1.5 m

- Ground outside, plus inside

System requirements

- Digital audio signal
- Connection cable

Package content

- Converter digital > analogue
- Power supply
- User manual

Images



Interface

Output:	2 x RCA female (red, white)
Input:	1 x TOSLINK female S/PDIF 1 x Coaxial female S/PDIF 1 x 5 V DC female 5,5 mm x 2,1 mm

Physical characteristics

Housing colour:	black
Housing material:	Plastic
Length:	63 mm
Width:	41 mm
Height:	21 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

